

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433571

Luminaire Tested: **LAMR4B108R609040DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R609040DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 824.7 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433571

CATALOG NUMBER: LAMR4B108R609040DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433571

CATALOG NUMBER: LAMR4B108R609040DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	467625
5°	451929
10°	447735
15°	436618
20°	402971
25°	360872
30°	279213
35°	167260
40°	64277
45°	23514
50°	921
55°	688
60°	789
65°	467
70°	577
75°	763
80°	1137
85°	0



TEST NUMBER: P433571

CATALOG NUMBER: LAMR4B108R609040DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.7	10.5
10°-20°	237.8	28.8
20°-30°	296.7	36.0
30°-40°	172.8	21.0
40°-50°	28.8	3.5
50°-60°	0.8	0.1
60°-70°	0.5	0.1
70°-80°	0.4	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	621.1	75.3
0°-40°	793.9	96.3
0°-60°	823.6	99.9
0°-90°	824.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	948	
5°	912	87
15°	855	238
25°	663	297
35°	278	173
45°	34	29
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433571

CATALOG NUMBER: LAMR4B108R609040DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	947.8
2.5°	932.2
5°	912.5
7.5°	901.3
10°	893.7
12.5°	881.3
15°	854.8
17.5°	815.1
20°	767.5
22.5°	719.0
25°	662.9
27.5°	585.1
30°	490.1
32.5°	383.9
35°	277.7
37.5°	175.1
40°	99.8
42.5°	58.5
45°	33.7
47.5°	11.6
50°	1.2
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)