

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433573

Luminaire Tested: **LAMR4B108R609050DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433573
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R609050DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 864.8 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433573

CATALOG NUMBER: LAMR4B108R609050DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433573

CATALOG NUMBER: LAMR4B108R609050DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82		
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67		
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63		
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59		
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	490419
5°	473968
10°	469529
15°	457918
20°	422608
25°	378456
30°	292829
35°	175452
40°	67433
45°	24630
50°	998
55°	688
60°	789
65°	467
70°	577
75°	763
80°	1137
85°	0



TEST NUMBER: P433573

CATALOG NUMBER: LAMR4B108R609050DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	10.5
10°-20°	249.4	28.8
20°-30°	311.1	36.0
30°-40°	181.3	21.0
40°-50°	30.3	3.5
50°-60°	0.8	0.1
60°-70°	0.5	0.1
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	651.4	75.3
0°-40°	832.7	96.3
0°-60°	863.7	99.9
0°-90°	864.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	864.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	994	
5°	957	91
15°	896	249
25°	695	311
35°	291	181
45°	35	30
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433573

CATALOG NUMBER: LAMR4B108R609050DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	994.0
2.5°	977.6
5°	957.0
7.5°	945.2
10°	937.2
12.5°	924.2
15°	896.5
17.5°	854.9
20°	804.9
22.5°	754.0
25°	695.2
27.5°	613.6
30°	514.0
32.5°	402.6
35°	291.3
37.5°	183.7
40°	104.7
42.5°	61.4
45°	35.3
47.5°	12.2
50°	1.3
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)