

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432083

Luminaire Tested: **LAM4B108R109040DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432083
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2008-908-1)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R109040DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 10 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 855.7 lumens
Efficiency: N/A
Efficacy: 75.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432083

CATALOG NUMBER: LAM4B108R109040DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P432083

CATALOG NUMBER: LAM4B108R109040DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	102	102	101	99	99	98	97	96		
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93		
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91		
6	103	98	95	93	102	98	95	92	97	94	92	95	93	91	94	92	91	90		
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	89		
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	88		
9	98	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87		
10	97	92	89	87	96	92	89	87	91	88	87	90	88	86	90	88	86	86		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6187769
5°	4156406
10°	1060798
15°	274598
20°	123018
25°	58521
30°	31391
35°	18250
40°	14234
45°	7675
50°	6371
55°	4731
60°	5427
65°	3269
70°	4039
75°	5338
80°	0
85°	0



TEST NUMBER: P432083

CATALOG NUMBER: LAM4B108R109040DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	576.8	67.4
10°-20°	183.6	21.5
20°-30°	53.6	6.3
30°-40°	20.4	2.4
40°-50°	9.7	1.1
50°-60°	5.8	0.7
60°-70°	3.1	0.4
70°-80°	2.6	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.0	95.1
0°-40°	834.4	97.5
0°-60°	850.0	99.3
0°-90°	855.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12542	
5°	8392	577
15°	538	184
25°	108	54
35°	30	20
45°	11	10
55°	6	6
65°	3	3
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P432083

CATALOG NUMBER: LAM4B108R109040DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	12541.6
1°	12420.3
2°	11918.5
3°	10961.8
4°	9779.1
5°	8392.3
6°	6859.4
7°	5445.1
8°	4066.6
9°	2963.8
10°	2117.4
11°	1499.8
12°	1111.1
13°	843.6
14°	670.0
15°	537.6
17.5°	350.1
20°	234.3
22.5°	157.1
25°	107.5
27.5°	74.4
30°	55.1
32.5°	38.6
35°	30.3
37.5°	24.8
40°	22.1
42.5°	16.5
45°	11.0
47.5°	8.3
50°	8.3
52.5°	8.3
55°	5.5
57.5°	5.5
60°	5.5
62.5°	2.8
65°	2.8
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	2.8
80°	0.0
82.5°	0.0



TEST NUMBER: P432083

CATALOG NUMBER: LAM4B108R109040DE010x1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)