

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432304

Luminaire Tested: **LAM4B108R559727DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R559727DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 678.1 lumens
Efficiency: N/A
Efficacy: 59.5 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432304

CATALOG NUMBER: LAM4B108R559727DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P432304

CATALOG NUMBER: LAM4B108R559727DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95						
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90						
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85						
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80						
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76						
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72						
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68						
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65						
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62						
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	456376
5°	462775
10°	473587
15°	453781
20°	412317
25°	331367
30°	190737
35°	55352
40°	8437
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P432304

CATALOG NUMBER: LAM4B108R559727DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.6	13.2
10°-20°	247.2	36.5
20°-30°	266.8	39.3
30°-40°	73.0	10.8
40°-50°	1.5	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.6	89.0
0°-40°	676.6	99.8
0°-60°	678.1	100.0
0°-90°	678.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	678.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	925	
5°	934	90
15°	888	247
25°	609	267
35°	92	73
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P432304

CATALOG NUMBER: LAM4B108R559727DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	925.0
2.5°	921.3
5°	934.4
7.5°	944.7
10°	945.3
12.5°	921.3
15°	888.4
17.5°	845.0
20°	785.3
22.5°	708.4
25°	608.7
27.5°	481.4
30°	334.8
32.5°	183.5
35°	91.9
37.5°	39.4
40°	13.1
42.5°	1.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)