

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432133

Luminaire Tested: **LAM4B108R209050DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R209050DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 919.1 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432133

CATALOG NUMBER: LAM4B108R209050DE010x1MB

Luminous Intensity Polar Plot



TEST NUMBER: P432133

CATALOG NUMBER: LAM4B108R209050DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97						
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95	94						
3	108	104	100	98	107	103	100	97	100	98	96	98	96	94	96	94	93	91						
4	105	100	97	94	104	99	96	93	97	94	92	96	93	91	94	92	90	89						
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87						
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85						
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83						
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82	81						
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80						
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79	78						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3174799
5°	2683539
10°	1576217
15°	564365
20°	186758
25°	74308
30°	35550
35°	20298
40°	14685
45°	12350
50°	14200
55°	11612
60°	5822
65°	4903
70°	6059
75°	6481
80°	4830
85°	4529



TEST NUMBER: P432133

CATALOG NUMBER: LAM4B108R209050DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	443.7	48.3
10°-20°	346.0	37.6
20°-30°	71.8	7.8
30°-40°	22.6	2.5
40°-50°	14.6	1.6
50°-60°	11.7	1.3
60°-70°	4.6	0.5
70°-80°	3.4	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	861.5	93.7
0°-40°	884.1	96.2
0°-60°	910.4	99.1
0°-90°	919.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	919.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6435	
5°	5418	444
15°	1105	346
25°	136	72
35°	34	23
45°	18	15
55°	14	12
65°	4	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P432133

CATALOG NUMBER: LAM4B108R209050DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	6434.8
2.5°	6198.8
5°	5418.4
7.5°	4341.3
10°	3146.2
12.5°	1984.8
15°	1104.9
17.5°	607.7
20°	355.7
22.5°	217.4
25°	136.5
27.5°	90.2
30°	62.4
32.5°	43.8
35°	33.7
37.5°	27.0
40°	22.8
42.5°	19.4
45°	17.7
47.5°	17.7
50°	18.5
52.5°	17.7
55°	13.5
57.5°	9.3
60°	5.9
62.5°	5.1
65°	4.2
67.5°	4.2
70°	4.2
72.5°	4.2
75°	3.4
77.5°	2.5
80°	1.7
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)