

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433387

Luminaire Tested: **LAMR4B108R209730DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R209730DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 727.1 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433387

CATALOG NUMBER: LAMR4B108R209730DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433387

CATALOG NUMBER: LAMR4B108R209730DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	109	108		107	106	105		103	102	101		100	99	99
2	112	108	105	103		110	106	104	102		103	101	100		101	99	97		98	97	95
3	108	104	100	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	105	100	97	94		104	99	96	93		97	94	92		96	93	91		94	92	90
5	103	97	93	90		101	96	93	90		95	92	89		93	91	89		92	90	88
6	100	94	90	88		99	94	90	87		92	89	87		91	88	86		90	88	86
7	98	92	88	85		97	91	88	85		90	87	85		89	86	84		88	86	84
8	96	90	86	83		95	89	86	83		88	85	83		87	85	82		87	84	82
9	94	88	84	81		93	87	84	81		86	83	81		86	83	81		85	82	81
10	92	86	82	80		91	85	82	80		85	82	79		84	81	79		83	81	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2511746
5°	2123049
10°	1247016
15°	446527
20°	147747
25°	58793
30°	28086
35°	16082
40°	11593
45°	9768
50°	11283
55°	9204
60°	4638
65°	3853
70°	4760
75°	5147
80°	3694
85°	3963



TEST NUMBER: P433387

CATALOG NUMBER: LAMR4B108R209730DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.0	48.3
10°-20°	273.7	37.6
20°-30°	56.8	7.8
30°-40°	17.9	2.5
40°-50°	11.5	1.6
50°-60°	9.3	1.3
60°-70°	3.6	0.5
70°-80°	2.7	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	681.6	93.7
0°-40°	699.5	96.2
0°-60°	720.2	99.1
0°-90°	727.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	727.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5091	
5°	4287	351
15°	874	274
25°	108	57
35°	27	18
45°	14	12
55°	11	9
65°	3	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P433387

CATALOG NUMBER: LAMR4B108R209730DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	5090.9
2.5°	4904.2
5°	4286.7
7.5°	3434.6
10°	2489.1
12.5°	1570.3
15°	874.2
17.5°	480.8
20°	281.4
22.5°	172.0
25°	108.0
27.5°	71.3
30°	49.3
32.5°	34.7
35°	26.7
37.5°	21.3
40°	18.0
42.5°	15.3
45°	14.0
47.5°	14.0
50°	14.7
52.5°	14.0
55°	10.7
57.5°	7.3
60°	4.7
62.5°	4.0
65°	3.3
67.5°	3.3
70°	3.3
72.5°	3.3
75°	2.7
77.5°	2.0
80°	1.3
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)