

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433532

Luminaire Tested: **LAMR4B108R509730DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R509730DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 50 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 779.6 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.74
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433532

CATALOG NUMBER: LAMR4B108R509730DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433532

CATALOG NUMBER: LAMR4B108R509730DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			
2	110	105	102	99	107	104	100	98	100	98	96	97	95	93	95	93	92	90			
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	84	82	81			
5	96	89	84	80	95	88	84	80	87	83	79	85	81	79	84	80	78	77			
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73			
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69			
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66			
9	82	73	68	65	81	73	68	65	72	68	64	71	67	64	70	67	64	63			
10	79	70	65	62	78	70	65	62	69	64	61	68	64	61	68	64	61	60			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206036
5°	196020
10°	190254
15°	182548
20°	150184
25°	120325
30°	62765
35°	20237
40°	3449
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P433532

CATALOG NUMBER: LAMR4B108R509730DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.1	14.6
10°-20°	296.2	38.0
20°-30°	288.2	37.0
30°-40°	79.3	10.2
40°-50°	1.7	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.5	89.6
0°-40°	777.8	99.8
0°-60°	779.6	100.0
0°-90°	779.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	779.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1279	
5°	1212	114
15°	1094	296
25°	677	288
35°	103	79
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433532

CATALOG NUMBER: LAMR4B108R509730DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1278.9
2.5°	1256.0
5°	1212.1
7.5°	1176.6
10°	1163.0
12.5°	1162.0
15°	1094.5
17.5°	970.1
20°	876.0
22.5°	797.9
25°	676.9
27.5°	476.5
30°	337.4
32.5°	204.2
35°	102.9
37.5°	46.0
40°	16.4
42.5°	1.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)