

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433579

Luminaire Tested: **LAMR4B108R609730DE010x1MB**

Issue Date: 11/23/2020


Test Information

Test Method: LM-41-14
Report Number: P433579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R609730DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 684.2 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433579

CATALOG NUMBER: LAMR4B108R609730DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433579

CATALOG NUMBER: LAMR4B108R609730DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96	106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88	101	96	91	88		93	89	86			91	87	85			88
4	98	91	85	81	96	90	85	81		88	83	80			86	82	79			84
5	93	85	80	75	92	84	79	75		83	78	74			81	77	74			79
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			75
7	84	75	70	66	83	75	69	65		74	69	65			72	68	65			71
8	80	71	65	61	79	71	65	61		70	65	61			69	64	61			68
9	77	67	62	58	76	67	61	58		66	61	57			65	60	57			64
10	73	64	58	54	72	63	58	54		62	58	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387994
5°	374965
10°	371485
15°	362299
20°	334348
25°	299411
30°	231699
35°	138771
40°	53328
45°	19467
50°	768
55°	602
60°	691
65°	350
70°	433
75°	572
80°	852
85°	0



TEST NUMBER: P433579

CATALOG NUMBER: LAMR4B108R609730DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.9	10.5
10°-20°	197.3	28.8
20°-30°	246.2	36.0
30°-40°	143.4	21.0
40°-50°	23.9	3.5
50°-60°	0.7	0.1
60°-70°	0.4	0.1
70°-80°	0.3	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.4	75.3
0°-40°	658.7	96.3
0°-60°	683.3	99.9
0°-90°	684.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	684.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	786	
5°	757	72
15°	709	197
25°	550	246
35°	230	143
45°	28	24
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433579

CATALOG NUMBER: LAMR4B108R609730DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	786.4
2.5°	773.4
5°	757.1
7.5°	747.8
10°	741.5
12.5°	731.2
15°	709.3
17.5°	676.3
20°	636.8
22.5°	596.5
25°	550.0
27.5°	485.5
30°	406.7
32.5°	318.5
35°	230.4
37.5°	145.3
40°	82.8
42.5°	48.5
45°	27.9
47.5°	9.6
50°	1.0
52.5°	0.7
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)