

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432164

Luminaire Tested: **LAM4B108R259730DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432164
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-5)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R259730DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 25 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 736.6 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432164

CATALOG NUMBER: LAM4B108R259730DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P432164

CATALOG NUMBER: LAM4B108R259730DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	103		110	107	104	102		104	102	100		101	99	98		98	97	96
3	109	104	101	99		107	103	100	98		101	98	96		99	96	95		96	95	93
4	106	101	97	95		104	100	97	94		98	95	93		96	94	92		94	93	91
5	103	98	94	91		102	97	93	91		95	92	90		94	91	89		92	90	89
6	100	95	91	88		99	94	91	88		93	90	87		92	89	87		91	88	86
7	98	92	88	86		97	92	88	86		91	87	85		90	87	85		89	86	84
8	96	90	86	83		95	89	86	83		88	85	83		88	85	83		87	84	82
9	94	88	84	81		93	87	84	81		86	83	81		86	83	81		85	82	81
10	91	85	82	79		91	85	82	79		84	81	79		84	81	79		83	81	79

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	579732
5°	540579
10°	428047
15°	215422
20°	69126
25°	24175
30°	8092
35°	1632
40°	526
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P432164

CATALOG NUMBER: LAM4B108R259730DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.9	40.2
10°-20°	358.9	48.7
20°-30°	73.0	9.9
30°-40°	8.3	1.1
40°-50°	0.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	727.9	98.8
0°-40°	736.2	99.9
0°-60°	736.6	100.0
0°-90°	736.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	736.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3598	
5°	3343	296
15°	1292	359
25°	136	73
35°	8	8
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P432164

CATALOG NUMBER: LAM4B108R259730DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3598.5
2.5°	3528.9
5°	3342.7
7.5°	3035.4
10°	2616.6
12.5°	2016.7
15°	1291.6
17.5°	727.6
20°	403.2
22.5°	229.7
25°	136.0
27.5°	81.3
30°	43.5
32.5°	19.1
35°	8.3
37.5°	5.1
40°	2.5
42.5°	1.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)