

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433627

Luminaire Tested: **LAMR4B108R709730DE010x1MB**

Issue Date: 11/23/2020


Test Information

Test Method: LM-41-14
Report Number: P433627
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R709730DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 704.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433627

CATALOG NUMBER: LAMR4B108R709730DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433627

CATALOG NUMBER: LAMR4B108R709730DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	92		104	99	95	91		96	92	89		93	90	87		90	88	86
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	85	79	74		92	84	78	74		82	77	73		80	76	72		78	74	71
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	61		68	64	60
7	78	68	61	56		77	67	61	56		66	60	56		65	60	56		63	59	55
8	74	63	57	52		73	63	56	52		62	56	52		60	55	51		59	55	51
9	70	59	53	48		69	59	52	48		58	52	48		57	51	48		56	51	47
10	66	55	49	45		65	55	49	44		54	48	44		53	48	44		52	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	255324
5°	250554
10°	253451
15°	260653
20°	261104
25°	236862
30°	211646
35°	185871
40°	136863
45°	76682
50°	37687
55°	21160
60°	12828
65°	8406
70°	6203
75°	5528
80°	3978
85°	3963



TEST NUMBER: P433627

CATALOG NUMBER: LAMR4B108R709730DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	6.9
10°-20°	143.8	20.4
20°-30°	199.5	28.3
30°-40°	187.7	26.7
40°-50°	89.6	12.7
50°-60°	23.7	3.4
60°-70°	7.5	1.1
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	391.7	55.6
0°-40°	579.4	82.3
0°-60°	692.7	98.4
0°-90°	704.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	704.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	506	48
15°	510	144
25°	435	200
35°	309	188
45°	110	90
55°	25	24
65°	7	7
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P433627

CATALOG NUMBER: LAMR4B108R709730DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	517.5
2.5°	511.0
5°	505.9
7.5°	505.2
10°	505.9
12.5°	507.4
15°	510.3
17.5°	510.3
20°	497.3
22.5°	469.8
25°	435.1
27.5°	400.4
30°	371.5
32.5°	343.3
35°	308.6
37.5°	263.8
40°	212.5
42.5°	158.3
45°	109.9
47.5°	73.0
50°	49.1
52.5°	34.0
55°	24.6
57.5°	17.3
60°	13.0
62.5°	9.4
65°	7.2
67.5°	5.1
70°	4.3
72.5°	3.6
75°	2.9
77.5°	2.2
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)