

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432622

Luminaire Tested: **LAM4B208R609024DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B208R609024DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1326.4 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432622

CATALOG NUMBER: LAM4B208R609024DE010x1MB

Luminous Intensity Polar Plot



TEST NUMBER: P432622

CATALOG NUMBER: LAM4B208R609024DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94						
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82						
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77						
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72						
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	69	67						
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63						
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59						
9	77	67	62	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56						
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	752157
5°	726899
10°	720174
15°	702277
20°	648114
25°	580422
30°	449099
35°	269050
40°	103372
45°	37748
50°	1458
55°	1118
60°	1283
65°	700
70°	866
75°	1144
80°	1705
85°	0



TEST NUMBER: P432622

CATALOG NUMBER: LAM4B208R609024DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.4	10.5
10°-20°	382.5	28.8
20°-30°	477.2	36.0
30°-40°	278.0	21.0
40°-50°	46.4	3.5
50°-60°	1.2	0.1
60°-70°	0.8	0.1
70°-80°	0.6	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	999.0	75.3
0°-40°	1277.0	96.3
0°-60°	1324.6	99.9
0°-90°	1326.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1326.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1524	
5°	1468	139
15°	1375	382
25°	1066	477
35°	447	278
45°	54	46
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P432622

CATALOG NUMBER: LAM4B208R609024DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1524.5
2.5°	1499.3
5°	1467.7
7.5°	1449.7
10°	1437.5
12.5°	1417.5
15°	1374.9
17.5°	1311.1
20°	1234.4
22.5°	1156.4
25°	1066.2
27.5°	941.1
30°	788.3
32.5°	617.5
35°	446.7
37.5°	281.7
40°	160.5
42.5°	94.1
45°	54.1
47.5°	18.7
50°	1.9
52.5°	1.3
55°	1.3
57.5°	1.3
60°	1.3
62.5°	1.3
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)