

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433340

Luminaire Tested: **LAMR4B108R109730DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2008-908-1)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R109730DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 10 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 710.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433340

CATALOG NUMBER: LAMR4B108R109730DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433340

CATALOG NUMBER: LAMR4B108R109730DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98		
2	113	110	107	105	111	108	106	104	105	103	102	102	101	99	99	98	97	96		
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	95	94		
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93		
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	96	94	92	91		
6	103	98	95	93	102	98	95	92	97	94	92	95	93	91	94	92	91	90		
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	89		
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	88		
9	98	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	87	87		
10	97	92	89	87	96	92	89	87	91	88	87	90	88	86	90	88	86	86		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5134058
5°	3448624
10°	880141
15°	227861
20°	102068
25°	48559
30°	26093
35°	15178
40°	11786
45°	6419
50°	5296
55°	3957
60°	4539
65°	2685
70°	3318
75°	4384
80°	0
85°	0



TEST NUMBER: P433340

CATALOG NUMBER: LAMR4B108R109730DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.5	67.4
10°-20°	152.4	21.5
20°-30°	44.5	6.3
30°-40°	16.9	2.4
40°-50°	8.1	1.1
50°-60°	4.9	0.7
60°-70°	2.6	0.4
70°-80°	2.1	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	675.4	95.1
0°-40°	692.3	97.5
0°-60°	705.3	99.3
0°-90°	710.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10406	
5°	6963	479
15°	446	152
25°	89	45
35°	25	17
45°	9	8
55°	5	5
65°	2	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P433340

CATALOG NUMBER: LAMR4B108R109730DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	10405.9
1°	10305.2
2°	9888.9
3°	9095.1
4°	8113.8
5°	6963.2
6°	5691.3
7°	4517.8
8°	3374.1
9°	2459.1
10°	1756.8
11°	1244.4
12°	921.9
13°	700.0
14°	555.9
15°	446.1
17.5°	290.5
20°	194.4
22.5°	130.4
25°	89.2
27.5°	61.8
30°	45.8
32.5°	32.0
35°	25.2
37.5°	20.6
40°	18.3
42.5°	13.7
45°	9.2
47.5°	6.9
50°	6.9
52.5°	6.9
55°	4.6
57.5°	4.6
60°	4.6
62.5°	2.3
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0



TEST NUMBER: P433340

CATALOG NUMBER: LAMR4B108R109730DE010x1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)