

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433727

Luminaire Tested: **LAMR4B208R309024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433727
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R309024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1421.0 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433727

CATALOG NUMBER: LAMR4B208R309024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433727

CATALOG NUMBER: LAMR4B208R309024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	91	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2574751
5°	2518517
10°	2183668
15°	1353425
20°	496061
25°	165819
30°	81411
35°	40595
40°	25183
45°	15978
50°	11360
55°	9290
60°	7993
65°	6304
70°	7790
75°	7625
80°	7671
85°	7359



TEST NUMBER: P433727

CATALOG NUMBER: LAMR4B208R309024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	463.4	32.6
10°-20°	699.7	49.2
20°-30°	170.6	12.0
30°-40°	46.7	3.3
40°-50°	18.8	1.3
50°-60°	10.1	0.7
60°-70°	6.0	0.4
70°-80°	4.6	0.3
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1333.7	93.9
0°-40°	1380.5	97.1
0°-60°	1409.3	99.2
0°-90°	1421.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1421.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5219	
5°	5085	463
15°	2650	700
25°	305	171
35°	67	47
45°	23	19
55°	11	10
65°	5	6
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P433727

CATALOG NUMBER: LAMR4B208R309024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	5218.6
2.5°	5183.5
5°	5085.2
7.5°	4850.6
10°	4358.7
12.5°	3587.8
15°	2649.7
17.5°	1707.6
20°	944.8
22.5°	504.1
25°	304.6
27.5°	206.2
30°	142.9
32.5°	97.0
35°	67.4
37.5°	49.9
40°	39.1
42.5°	29.7
45°	22.9
47.5°	18.9
50°	14.8
52.5°	13.5
55°	10.8
57.5°	9.4
60°	8.1
62.5°	6.7
65°	5.4
67.5°	5.4
70°	5.4
72.5°	5.4
75°	4.0
77.5°	4.0
80°	2.7
82.5°	1.3
85°	1.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)