

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433823

Luminaire Tested: **LAMR4B208R509024DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R509024DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 50 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1511.2 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.74
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433823

CATALOG NUMBER: LAMR4B208R509024DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433823

CATALOG NUMBER: LAMR4B208R509024DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	110	105	102	99		107	104	100	98		100	98	96			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	89	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	83	79			85	81	79			84
6	92	85	80	76		91	84	79	76		83	78	75			81	77	75			80
7	89	81	75	72		87	80	75	72		79	74	71			78	74	71			77
8	85	77	72	68		84	76	71	68		75	71	68			74	70	67			73
9	82	73	68	65		81	73	68	65		72	68	64			71	67	64			70
10	79	70	65	62		78	70	65	62		69	64	61			68	64	61			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	399409
5°	379975
10°	368812
15°	353872
20°	291128
25°	233272
30°	121680
35°	39236
40°	6667
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P433823

CATALOG NUMBER: LAMR4B208R509024DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.2	14.6
10°-20°	574.2	38.0
20°-30°	558.6	37.0
30°-40°	153.8	10.2
40°-50°	3.3	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1354.1	89.6
0°-40°	1507.8	99.8
0°-60°	1511.2	100.0
0°-90°	1511.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1511.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2479	
5°	2350	221
15°	2122	574
25°	1312	559
35°	200	154
45°	0	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433823

CATALOG NUMBER: LAMR4B208R509024DE010x1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2479.2
2.5°	2434.9
5°	2349.6
7.5°	2280.9
10°	2254.5
12.5°	2252.5
15°	2121.7
17.5°	1880.5
20°	1698.1
22.5°	1546.8
25°	1312.3
27.5°	923.7
30°	654.1
32.5°	395.8
35°	199.5
37.5°	89.2
40°	31.7
42.5°	2.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)