

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433730

Luminaire Tested: **LAMR4B208R309027DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433730
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R309027DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1550.0 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433730

CATALOG NUMBER: LAMR4B208R309027DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433730

CATALOG NUMBER: LAMR4B208R309027DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2808267
5°	2746933
10°	2381710
15°	1476166
20°	541057
25°	180844
30°	88760
35°	44269
40°	27437
45°	17444
50°	12435
55°	10150
60°	8683
65°	6888
70°	8511
75°	8388
80°	8240
85°	8491



TEST NUMBER: P433730

CATALOG NUMBER: LAMR4B208R309027DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.5	32.6
10°-20°	763.2	49.2
20°-30°	186.1	12.0
30°-40°	50.9	3.3
40°-50°	20.5	1.3
50°-60°	11.0	0.7
60°-70°	6.6	0.4
70°-80°	5.0	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1454.7	93.9
0°-40°	1505.6	97.1
0°-60°	1537.1	99.2
0°-90°	1550.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1550.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5692	
5°	5546	505
15°	2890	763
25°	332	186
35°	74	51
45°	25	21
55°	12	11
65°	6	7
75°	4	5
85°	2	1
90°	0	



TEST NUMBER: P433730

CATALOG NUMBER: LAMR4B208R309027DE010x1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5691.9
2.5°	5653.7
5°	5546.4
7.5°	5290.6
10°	4754.0
12.5°	3913.2
15°	2890.0
17.5°	1862.5
20°	1030.5
22.5°	549.8
25°	332.2
27.5°	224.9
30°	155.8
32.5°	105.8
35°	73.5
37.5°	54.4
40°	42.6
42.5°	32.3
45°	25.0
47.5°	20.6
50°	16.2
52.5°	14.7
55°	11.8
57.5°	10.3
60°	8.8
62.5°	7.4
65°	5.9
67.5°	5.9
70°	5.9
72.5°	5.9
75°	4.4
77.5°	4.4
80°	2.9
82.5°	1.5
85°	1.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)