

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433780

Luminaire Tested: **LAMR4B208R409030DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433780
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R409030DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1693.3 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433780

CATALOG NUMBER: LAMR4B208R409030DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433780

CATALOG NUMBER: LAMR4B208R409030DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	102	100		102	100	98		99	97	96		97	95	94
3	107	102	98	95		105	101	97	94		98	95	93		96	94	92		94	92	90
4	103	98	93	90		102	97	93	90		95	91	89		93	90	88		91	89	87
5	100	94	89	86		98	93	89	86		91	88	85		90	87	84		88	86	84
6	97	90	85	82		95	89	85	82		88	84	82		87	83	81		85	83	80
7	93	87	82	79		92	86	82	79		85	81	78		84	80	78		83	80	78
8	91	83	79	76		90	83	79	76		82	78	75		81	78	75		80	77	75
9	88	81	76	73		87	80	76	73		79	75	73		79	75	73		78	75	72
10	85	78	73	71		84	77	73	70		77	73	70		76	73	70		75	72	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	638374
5°	641621
10°	637065
15°	574731
20°	362602
25°	130599
30°	27365
35°	8319
40°	1661
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P433780

CATALOG NUMBER: LAMR4B208R409030DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.2	22.2
10°-20°	899.6	53.1
20°-30°	383.6	22.7
30°-40°	32.9	1.9
40°-50°	1.0	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1659.4	98.0
0°-40°	1692.3	99.9
0°-60°	1693.3	100.0
0°-90°	1693.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1693.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3962	
5°	3968	376
15°	3446	900
25°	735	384
35°	42	33
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433780

CATALOG NUMBER: LAMR4B208R409030DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3962.5
2.5°	3958.9
5°	3967.5
7.5°	3943.8
10°	3894.3
12.5°	3746.5
15°	3445.9
17.5°	2859.0
20°	2115.0
22.5°	1392.6
25°	734.7
27.5°	297.7
30°	147.1
32.5°	78.2
35°	42.3
37.5°	21.5
40°	7.9
42.5°	1.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)