

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433926

Luminaire Tested: **LAMR4B208R709030DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R709030DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1531.0 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433926

CATALOG NUMBER: LAMR4B208R709030DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P433926

CATALOG NUMBER: LAMR4B208R709030DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	555249
5°	544890
10°	551190
15°	566817
20°	567782
25°	515096
30°	460265
35°	404207
40°	297621
45°	166691
50°	82052
55°	45934
60°	27925
65°	18329
70°	13560
75°	12010
80°	8808
85°	9057



TEST NUMBER: P433926

CATALOG NUMBER: LAMR4B208R709030DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.2	6.9
10°-20°	312.7	20.4
20°-30°	433.9	28.3
30°-40°	408.2	26.7
40°-50°	194.9	12.7
50°-60°	51.5	3.4
60°-70°	16.2	1.1
70°-80°	6.6	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	851.8	55.6
0°-40°	1260.0	82.3
0°-60°	1506.4	98.4
0°-90°	1531.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1531.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1125	
5°	1100	105
15°	1110	313
25°	946	434
35°	671	408
45°	239	195
55°	53	52
65°	16	16
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P433926

CATALOG NUMBER: LAMR4B208R709030DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1125.4
2.5°	1111.2
5°	1100.2
7.5°	1098.7
10°	1100.2
12.5°	1103.4
15°	1109.7
17.5°	1109.7
20°	1081.4
22.5°	1021.6
25°	946.2
27.5°	870.8
30°	807.9
32.5°	746.6
35°	671.1
37.5°	573.7
40°	462.1
42.5°	344.2
45°	238.9
47.5°	158.7
50°	106.9
52.5°	73.9
55°	53.4
57.5°	37.7
60°	28.3
62.5°	20.4
65°	15.7
67.5°	11.0
70°	9.4
72.5°	7.9
75°	6.3
77.5°	4.7
80°	3.1
82.5°	3.1
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)