

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432537

Luminaire Tested: **LAM4B208R409035DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B208R409035DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1773.8 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432537

CATALOG NUMBER: LAM4B208R409035DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P432537

CATALOG NUMBER: LAM4B208R409035DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80
9	88	81	76	73	87	80	76	73	79	75	73		79	75	73		78
10	85	78	73	71	84	77	73	70	77	73	70		76	73	70		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	668710
5°	672105
10°	667345
15°	602051
20°	379849
25°	136803
30°	28667
35°	8713
40°	1746
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P432537

CATALOG NUMBER: LAM4B208R409035DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	394.1	22.2
10°-20°	942.4	53.1
20°-30°	401.8	22.7
30°-40°	34.4	1.9
40°-50°	1.0	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1738.3	98.0
0°-40°	1772.8	99.9
0°-60°	1773.8	100.0
0°-90°	1773.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1773.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4151	
5°	4156	394
15°	3610	942
25°	770	402
35°	44	34
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P432537

CATALOG NUMBER: LAM4B208R409035DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4150.8
2.5°	4147.0
5°	4156.0
7.5°	4131.2
10°	4079.4
12.5°	3924.6
15°	3609.7
17.5°	2994.9
20°	2215.6
22.5°	1458.7
25°	769.6
27.5°	311.9
30°	154.1
32.5°	81.9
35°	44.3
37.5°	22.5
40°	8.3
42.5°	1.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)