

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433879

Luminaire Tested: **LAMR4B208R609035DE010x1MB**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P433879  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B208R609035DE010x1MB  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1558.8 lumens  
Efficiency: N/A  
Efficacy: 75.7 lumens/watt  
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P433879

CATALOG NUMBER: LAMR4B208R609035DE010x1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P433879

CATALOG NUMBER: LAMR4B208R609035DE010x1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  | 96  | 93  | 91  | 93  | 91  | 89  | 88  |    |    |
| 3   | 103 | 97  | 92  | 88  | 101 | 96  | 91  | 88  | 93  | 89  | 86  | 91  | 87  | 85  | 88  | 86  | 84  | 82  |    |    |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 88  | 83  | 80  | 86  | 82  | 79  | 84  | 81  | 78  | 77  |    |    |
| 5   | 93  | 85  | 80  | 75  | 92  | 84  | 79  | 75  | 83  | 78  | 74  | 81  | 77  | 74  | 79  | 76  | 73  | 72  |    |    |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 69  | 67  |    |    |
| 7   | 84  | 75  | 70  | 66  | 83  | 75  | 69  | 65  | 74  | 69  | 65  | 72  | 68  | 65  | 71  | 67  | 64  | 63  |    |    |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 60  | 59  |    |    |
| 9   | 77  | 67  | 62  | 58  | 76  | 67  | 61  | 58  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 56  |    |    |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 58  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 53  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 883840 |
| 5°  | 854232 |
| 10° | 846274 |
| 15° | 825274 |
| 20° | 761628 |
| 25° | 682059 |
| 30° | 527775 |
| 35° | 316150 |
| 40° | 121470 |
| 45° | 44377  |
| 50° | 1765   |
| 55° | 1290   |
| 60° | 1480   |
| 65° | 934    |
| 70° | 1154   |
| 75° | 1525   |
| 80° | 2273   |
| 85° | 0      |



TEST NUMBER: P433879

CATALOG NUMBER: LAMR4B208R609035DE010x1MB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 163.8  | 10.5      |
| 10°-20°   | 449.5  | 28.8      |
| 20°-30°   | 560.7  | 36.0      |
| 30°-40°   | 326.7  | 21.0      |
| 40°-50°   | 54.5   | 3.5       |
| 50°-60°   | 1.4    | 0.1       |
| 60°-70°   | 1.0    | 0.1       |
| 70°-80°   | 0.8    | 0.1       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1174.0 | 75.3      |
| 0°-40°    | 1500.6 | 96.3      |
| 0°-60°    | 1556.6 | 99.9      |
| 0°-90°    | 1558.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1558.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1791 |      |
| 5°  | 1725 | 164  |
| 15° | 1616 | 449  |
| 25° | 1253 | 561  |
| 35° | 525  | 327  |
| 45° | 64   | 55   |
| 55° | 2    | 1    |
| 65° | 1    | 1    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P433879

CATALOG NUMBER: LAMR4B208R609035DE010x1MB

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1791.4 |
| 2.5°  | 1761.9 |
| 5°    | 1724.8 |
| 7.5°  | 1703.6 |
| 10°   | 1689.2 |
| 12.5° | 1665.7 |
| 15°   | 1615.7 |
| 17.5° | 1540.7 |
| 20°   | 1450.6 |
| 22.5° | 1358.9 |
| 25°   | 1252.9 |
| 27.5° | 1105.9 |
| 30°   | 926.4  |
| 32.5° | 725.7  |
| 35°   | 524.9  |
| 37.5° | 331.0  |
| 40°   | 188.6  |
| 42.5° | 110.6  |
| 45°   | 63.6   |
| 47.5° | 22.0   |
| 50°   | 2.3    |
| 52.5° | 1.5    |
| 55°   | 1.5    |
| 57.5° | 1.5    |
| 60°   | 1.5    |
| 62.5° | 1.5    |
| 65°   | 0.8    |
| 67.5° | 0.8    |
| 70°   | 0.8    |
| 72.5° | 0.8    |
| 75°   | 0.8    |
| 77.5° | 0.8    |
| 80°   | 0.8    |
| 82.5° | 0.8    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)