

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433856

Luminaire Tested: **LAMR4B208R559035DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R559035DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1655.2 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433856

CATALOG NUMBER: LAMR4B208R559035DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433856

CATALOG NUMBER: LAMR4B208R559035DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	83	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	75	70	67	74	70	67		73	69	66		73
9	81	72	67	64	80	72	67	63	71	66	63		70	66	63		69
10	78	69	64	60	77	69	64	60	68	63	60		67	63	60		66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1114051
5°	1129648
10°	1156086
15°	1107737
20°	1006456
25°	808791
30°	465620
35°	135097
40°	20610
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P433856

CATALOG NUMBER: LAMR4B208R559035DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.7	13.2
10°-20°	603.4	36.5
20°-30°	651.3	39.3
30°-40°	178.1	10.8
40°-50°	3.7	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1473.4	89.0
0°-40°	1651.5	99.8
0°-60°	1655.2	100.0
0°-90°	1655.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1655.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2258	
5°	2281	219
15°	2169	603
25°	1486	651
35°	224	178
45°	0	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433856

CATALOG NUMBER: LAMR4B208R559035DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2258.0
2.5°	2248.8
5°	2280.9
7.5°	2306.1
10°	2307.6
12.5°	2248.8
15°	2168.7
17.5°	2062.6
20°	1916.9
22.5°	1729.2
25°	1485.7
27.5°	1175.2
30°	817.3
32.5°	447.9
35°	224.3
37.5°	96.1
40°	32.0
42.5°	4.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)