

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432491

Luminaire Tested: **LAM4B208R309040DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432491
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B208R309040DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1775.7 lumens
Efficiency: N/A
Efficacy: 86.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432491

CATALOG NUMBER: LAM4B208R309040DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P432491

CATALOG NUMBER: LAM4B208R309040DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	91	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3217377
5°	3147107
10°	2728696
15°	1691257
20°	619866
25°	207193
30°	101692
35°	50714
40°	31430
45°	19955
50°	14200
55°	11612
60°	9966
65°	7822
70°	9665
75°	9722
80°	9660
85°	9624



TEST NUMBER: P432491

CATALOG NUMBER: LAM4B208R309040DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	579.1	32.6
10°-20°	874.3	49.2
20°-30°	213.2	12.0
30°-40°	58.4	3.3
40°-50°	23.5	1.3
50°-60°	12.6	0.7
60°-70°	7.5	0.4
70°-80°	5.8	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1666.6	93.9
0°-40°	1725.0	97.1
0°-60°	1761.1	99.2
0°-90°	1775.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1775.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6521	
5°	6354	579
15°	3311	874
25°	381	213
35°	84	58
45°	29	23
55°	14	13
65°	7	7
75°	5	6
85°	2	1
90°	0	



TEST NUMBER: P432491

CATALOG NUMBER: LAM4B208R309040DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6521.1
2.5°	6477.3
5°	6354.4
7.5°	6061.4
10°	5446.6
12.5°	4483.3
15°	3311.1
17.5°	2133.9
20°	1180.6
22.5°	629.9
25°	380.6
27.5°	257.7
30°	178.5
32.5°	121.3
35°	84.2
37.5°	62.3
40°	48.8
42.5°	37.1
45°	28.6
47.5°	23.6
50°	18.5
52.5°	16.8
55°	13.5
57.5°	11.8
60°	10.1
62.5°	8.4
65°	6.7
67.5°	6.7
70°	6.7
72.5°	6.7
75°	5.1
77.5°	5.1
80°	3.4
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)