

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433884

Luminaire Tested: **LAMR4B208R609040DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R609040DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1657.5 lumens
Efficiency: N/A
Efficacy: 80.5 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433884

CATALOG NUMBER: LAMR4B208R609040DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P433884

CATALOG NUMBER: LAMR4B208R609040DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	106	111	109	107	105		105	103	102			101	100	99			98
2	108	104	100	96	106	102	98	95		99	96	93			96	93	91			93
3	103	97	92	88	101	96	91	88		93	89	86			91	87	85			88
4	98	91	85	81	96	90	85	81		88	83	80			86	82	79			84
5	93	85	80	75	92	84	79	75		83	78	74			81	77	74			79
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			75
7	84	75	70	66	83	75	69	65		74	69	65			72	68	65			71
8	80	71	65	61	79	71	65	61		70	65	61			69	64	61			68
9	77	67	62	58	76	67	61	58		66	61	57			65	60	57			64
10	73	64	58	54	72	63	58	54		62	58	54			62	57	54			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	939888
5°	908364
10°	899880
15°	877578
20°	809880
25°	725283
30°	561217
35°	336207
40°	129199
45°	47237
50°	1842
55°	1376
60°	1579
65°	934
70°	1154
75°	1525
80°	2273
85°	0



TEST NUMBER: P433884

CATALOG NUMBER: LAMR4B208R609040DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.2	10.5
10°-20°	478.0	28.8
20°-30°	596.3	36.0
30°-40°	347.4	21.0
40°-50°	58.0	3.5
50°-60°	1.5	0.1
60°-70°	1.1	0.1
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1248.4	75.3
0°-40°	1595.8	96.3
0°-60°	1655.3	99.9
0°-90°	1657.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1657.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1905	
5°	1834	174
15°	1718	478
25°	1332	596
35°	558	347
45°	68	58
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P433884

CATALOG NUMBER: LAMR4B208R609040DE010x1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1905.0
2.5°	1873.6
5°	1834.1
7.5°	1811.5
10°	1796.2
12.5°	1771.3
15°	1718.1
17.5°	1638.4
20°	1542.5
22.5°	1445.0
25°	1332.3
27.5°	1176.0
30°	985.1
32.5°	771.7
35°	558.2
37.5°	352.0
40°	200.6
42.5°	117.6
45°	67.7
47.5°	23.4
50°	2.4
52.5°	1.6
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.6
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)