

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433886

Luminaire Tested: **LAMR4B208R609050DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R609050DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1738.2 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433886

CATALOG NUMBER: LAMR4B208R609050DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433886

CATALOG NUMBER: LAMR4B208R609050DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	985674
5°	952641
10°	943766
15°	920331
20°	849363
25°	760613
30°	588563
35°	352589
40°	135446
45°	49540
50°	1919
55°	1462
60°	1677
65°	934
70°	1154
75°	1525
80°	2273
85°	0



TEST NUMBER: P433886

CATALOG NUMBER: LAMR4B208R609050DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.7	10.5
10°-20°	501.3	28.8
20°-30°	625.3	36.0
30°-40°	364.3	21.0
40°-50°	60.8	3.5
50°-60°	1.6	0.1
60°-70°	1.1	0.1
70°-80°	0.8	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1309.2	75.3
0°-40°	1673.5	96.3
0°-60°	1735.9	99.9
0°-90°	1738.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1738.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1998	
5°	1924	183
15°	1802	501
25°	1397	625
35°	585	364
45°	71	61
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P433886

CATALOG NUMBER: LAMR4B208R609050DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1997.8
2.5°	1964.9
5°	1923.5
7.5°	1899.8
10°	1883.8
12.5°	1857.6
15°	1801.8
17.5°	1718.2
20°	1617.7
22.5°	1515.5
25°	1397.2
27.5°	1233.3
30°	1033.1
32.5°	809.3
35°	585.4
37.5°	369.2
40°	210.3
42.5°	123.3
45°	71.0
47.5°	24.5
50°	2.5
52.5°	1.7
55°	1.7
57.5°	1.7
60°	1.7
62.5°	1.7
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)