

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432640

Luminaire Tested: **LAM4B208R609727DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432640
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B208R609727DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1283.4 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432640

CATALOG NUMBER: LAM4B208R609727DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P432640

CATALOG NUMBER: LAM4B208R609727DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	727735
5°	703374
10°	696778
15°	679496
20°	627112
25°	561587
30°	434571
35°	260316
40°	100023
45°	36562
50°	1458
55°	1032
60°	1184
65°	700
70°	866
75°	1144
80°	1705
85°	0



TEST NUMBER: P432640

CATALOG NUMBER: LAM4B208R609727DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	10.5
10°-20°	370.1	28.8
20°-30°	461.7	36.0
30°-40°	269.0	21.0
40°-50°	44.9	3.5
50°-60°	1.2	0.1
60°-70°	0.8	0.1
70°-80°	0.6	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	966.6	75.3
0°-40°	1235.6	96.3
0°-60°	1281.7	99.9
0°-90°	1283.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1475	
5°	1420	135
15°	1330	370
25°	1032	462
35°	432	269
45°	52	45
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P432640

CATALOG NUMBER: LAM4B208R609727DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1475.0
2.5°	1450.7
5°	1420.2
7.5°	1402.7
10°	1390.8
12.5°	1371.5
15°	1330.3
17.5°	1268.6
20°	1194.4
22.5°	1118.9
25°	1031.6
27.5°	910.6
30°	762.8
32.5°	597.5
35°	432.2
37.5°	272.6
40°	155.3
42.5°	91.1
45°	52.4
47.5°	18.1
50°	1.9
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)