

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433817

Luminaire Tested: **LAMR4B208R459727DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433817
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R459727DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1360.7 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433817

CATALOG NUMBER: LAMR4B208R459727DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433817

CATALOG NUMBER: LAMR4B208R459727DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	94	91	103	98	93	90	95	92	89		93	90	87		90
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	79	76	91	84	79	75	82	78	75		81	77	74		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1257427
5°	1256980
10°	1194763
15°	1049508
20°	802897
25°	468715
30°	191820
35°	81131
40°	44247
45°	28538
50°	22336
55°	19268
60°	15591
65°	12375
70°	11396
75°	10103
80°	11365
85°	7359



TEST NUMBER: P433817

CATALOG NUMBER: LAMR4B208R459727DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.5	17.5
10°-20°	559.4	41.1
20°-30°	394.1	29.0
30°-40°	97.0	7.1
40°-50°	33.8	2.5
50°-60°	20.0	1.5
60°-70°	11.1	0.8
70°-80°	6.1	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.0	87.5
0°-40°	1288.0	94.7
0°-60°	1341.9	98.6
0°-90°	1360.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1360.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2549	
5°	2538	237
15°	2055	559
25°	861	394
35°	135	97
45°	41	34
55°	22	20
65°	11	11
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P433817

CATALOG NUMBER: LAMR4B208R459727DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2548.6
2.5°	2542.0
5°	2538.0
7.5°	2491.8
10°	2384.8
12.5°	2239.6
15°	2054.7
17.5°	1815.7
20°	1529.2
22.5°	1200.3
25°	861.0
27.5°	555.9
30°	336.7
32.5°	204.7
35°	134.7
37.5°	95.1
40°	68.7
42.5°	52.8
45°	40.9
47.5°	34.3
50°	29.1
52.5°	25.1
55°	22.4
57.5°	19.8
60°	15.8
62.5°	13.2
65°	10.6
67.5°	9.2
70°	7.9
72.5°	6.6
75°	5.3
77.5°	5.3
80°	4.0
82.5°	2.6
85°	1.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)