

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433677

Luminaire Tested: **LAMR4B208R159730DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P433677  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-6)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B208R159730DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 15 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1449.2 lumens  
Efficiency: N/A  
Efficacy: 70.3 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.29' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P433677

CATALOG NUMBER: LAMR4B208R159730DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P433677

CATALOG NUMBER: LAMR4B208R159730DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 |  | 108 | 107 | 106 |  |  | 104 | 103 | 103 |  |  | 101 |
| 2   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 104 |  | 105 | 103 | 102 |  |  | 102 | 101 | 100 |  |  | 100 |
| 3   | 110 | 106 | 103 | 101 | 108 | 105 | 102 | 100 |  | 103 | 100 | 98  |  |  | 100 | 99  | 97  |  |  | 98  |
| 4   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 97  |  | 100 | 98  | 96  |  |  | 98  | 96  | 95  |  |  | 97  |
| 5   | 105 | 101 | 97  | 95  | 104 | 100 | 97  | 94  |  | 98  | 96  | 94  |  |  | 97  | 95  | 93  |  |  | 95  |
| 6   | 103 | 98  | 95  | 92  | 102 | 98  | 94  | 92  |  | 96  | 94  | 92  |  |  | 95  | 93  | 91  |  |  | 94  |
| 7   | 101 | 96  | 93  | 90  | 100 | 96  | 92  | 90  |  | 95  | 92  | 90  |  |  | 94  | 91  | 89  |  |  | 93  |
| 8   | 99  | 94  | 91  | 89  | 99  | 94  | 91  | 89  |  | 93  | 90  | 88  |  |  | 92  | 90  | 88  |  |  | 91  |
| 9   | 98  | 92  | 89  | 87  | 97  | 92  | 89  | 87  |  | 91  | 89  | 87  |  |  | 91  | 88  | 87  |  |  | 90  |
| 10  | 96  | 91  | 88  | 86  | 95  | 91  | 88  | 86  |  | 90  | 87  | 85  |  |  | 89  | 87  | 85  |  |  | 89  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2072971 |
| 5°  | 1749511 |
| 10° | 803762  |
| 15° | 250631  |
| 20° | 102129  |
| 25° | 33507   |
| 30° | 10380   |
| 35° | 2203    |
| 40° | 547     |
| 45° | 0       |
| 50° | 0       |
| 55° | 0       |
| 60° | 0       |
| 65° | 0       |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P433677

CATALOG NUMBER: LAMR4B208R159730DE010x1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 834.8  | 57.6      |
| 10°-20°   | 497.5  | 34.3      |
| 20°-30°   | 105.4  | 7.3       |
| 30°-40°   | 11.1   | 0.8       |
| 40°-50°   | 0.4    | 0.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1437.7 | 99.2      |
| 0°-40°    | 1448.8 | 100.0     |
| 0°-60°    | 1449.2 | 100.0     |
| 0°-90°    | 1449.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1449.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 12867 |      |
| 5°  | 10818 | 835  |
| 15° | 1503  | 498  |
| 25° | 188   | 105  |
| 35° | 11    | 11   |
| 45° | 0     | 0    |
| 55° | 0     | 0    |
| 65° | 0     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P433677

CATALOG NUMBER: LAMR4B208R159730DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 12867.3 |
| 2.5°  | 12460.8 |
| 5°    | 10818.2 |
| 7.5°  | 8008.6  |
| 10°   | 4913.3  |
| 12.5° | 2621.8  |
| 15°   | 1502.7  |
| 17.5° | 943.8   |
| 20°   | 595.7   |
| 22.5° | 351.4   |
| 25°   | 188.5   |
| 27.5° | 106.4   |
| 30°   | 55.8    |
| 32.5° | 28.2    |
| 35°   | 11.2    |
| 37.5° | 5.9     |
| 40°   | 2.6     |
| 42.5° | 0.7     |
| 45°   | 0.0     |
| 47.5° | 0.0     |
| 50°   | 0.0     |
| 52.5° | 0.0     |
| 55°   | 0.0     |
| 57.5° | 0.0     |
| 60°   | 0.0     |
| 62.5° | 0.0     |
| 65°   | 0.0     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)