

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433653

Luminaire Tested: **LAMR4B208R109730DE010x1MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P433653  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2008-908-1)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B208R109730DE010x1MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 10 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1426.9 lumens  
Efficiency: N/A  
Efficacy: 69.3 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P433653

CATALOG NUMBER: LAMR4B208R109730DE010x1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P433653

CATALOG NUMBER: LAMR4B208R109730DE010x1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 116 | 114 | 112 | 111 |  | 113 | 112 | 110 | 109 |  | 108 | 107 | 106 |  | 104 | 103 | 103 |  | 101 | 100 | 100 |
| 2   | 113 | 110 | 107 | 105 |  | 111 | 108 | 106 | 104 |  | 105 | 103 | 102 |  | 102 | 101 | 99  |  | 99  | 98  | 97  |
| 3   | 110 | 106 | 103 | 101 |  | 108 | 105 | 102 | 100 |  | 102 | 100 | 98  |  | 100 | 98  | 97  |  | 98  | 97  | 95  |
| 4   | 108 | 103 | 100 | 97  |  | 106 | 102 | 99  | 97  |  | 100 | 98  | 96  |  | 98  | 96  | 95  |  | 97  | 95  | 94  |
| 5   | 105 | 101 | 97  | 95  |  | 104 | 100 | 97  | 94  |  | 98  | 96  | 94  |  | 97  | 95  | 93  |  | 96  | 94  | 92  |
| 6   | 103 | 98  | 95  | 93  |  | 102 | 98  | 95  | 92  |  | 97  | 94  | 92  |  | 95  | 93  | 91  |  | 94  | 92  | 91  |
| 7   | 102 | 97  | 93  | 91  |  | 101 | 96  | 93  | 91  |  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  | 91  | 90  |
| 8   | 100 | 95  | 92  | 89  |  | 99  | 94  | 91  | 89  |  | 94  | 91  | 89  |  | 93  | 90  | 89  |  | 92  | 90  | 88  |
| 9   | 98  | 93  | 90  | 88  |  | 98  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 92  | 89  | 88  |  | 91  | 89  | 87  |
| 10  | 97  | 92  | 89  | 87  |  | 96  | 92  | 89  | 87  |  | 91  | 88  | 87  |  | 90  | 88  | 86  |  | 90  | 88  | 86  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |          |
|-----|----------|
|     | 0°       |
| 0°  | 10318984 |
| 5°  | 6931371  |
| 10° | 1768998  |
| 15° | 457918   |
| 20° | 205187   |
| 25° | 97608    |
| 30° | 52413    |
| 35° | 30477    |
| 40° | 23701    |
| 45° | 12838    |
| 50° | 10592    |
| 55° | 7914     |
| 60° | 9078     |
| 65° | 5370     |
| 70° | 6636     |
| 75° | 8769     |
| 80° | 0        |
| 85° | 0        |



TEST NUMBER: P433653

CATALOG NUMBER: LAMR4B208R109730DE010x1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 961.8  | 67.4      |
| 10°-20°   | 306.2  | 21.5      |
| 20°-30°   | 89.4   | 6.3       |
| 30°-40°   | 34.0   | 2.4       |
| 40°-50°   | 16.2   | 1.1       |
| 50°-60°   | 9.7    | 0.7       |
| 60°-70°   | 5.1    | 0.4       |
| 70°-80°   | 4.2    | 0.3       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1357.5 | 95.1      |
| 0°-40°    | 1391.5 | 97.5      |
| 0°-60°    | 1417.5 | 99.3      |
| 0°-90°    | 1426.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1426.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 20915 |      |
| 5°  | 13995 | 962  |
| 15° | 896   | 306  |
| 25° | 179   | 89   |
| 35° | 51    | 34   |
| 45° | 18    | 16   |
| 55° | 9     | 10   |
| 65° | 5     | 5    |
| 75° | 5     | 4    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P433653

CATALOG NUMBER: LAMR4B208R109730DE010x1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 20914.9 |
| 1°    | 20712.6 |
| 2°    | 19875.8 |
| 3°    | 18280.4 |
| 4°    | 16308.0 |
| 5°    | 13995.3 |
| 6°    | 11439.0 |
| 7°    | 9080.4  |
| 8°    | 6781.6  |
| 9°    | 4942.5  |
| 10°   | 3531.0  |
| 11°   | 2501.1  |
| 12°   | 1852.9  |
| 13°   | 1406.9  |
| 14°   | 1117.2  |
| 15°   | 896.5   |
| 17.5° | 583.9   |
| 20°   | 390.8   |
| 22.5° | 262.1   |
| 25°   | 179.3   |
| 27.5° | 124.1   |
| 30°   | 92.0    |
| 32.5° | 64.4    |
| 35°   | 50.6    |
| 37.5° | 41.4    |
| 40°   | 36.8    |
| 42.5° | 27.6    |
| 45°   | 18.4    |
| 47.5° | 13.8    |
| 50°   | 13.8    |
| 52.5° | 13.8    |
| 55°   | 9.2     |
| 57.5° | 9.2     |
| 60°   | 9.2     |
| 62.5° | 4.6     |
| 65°   | 4.6     |
| 67.5° | 4.6     |
| 70°   | 4.6     |
| 72.5° | 4.6     |
| 75°   | 4.6     |
| 77.5° | 4.6     |
| 80°   | 0.0     |
| 82.5° | 0.0     |



TEST NUMBER: P433653

CATALOG NUMBER: LAMR4B208R109730DE010x1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







|       |     |
|-------|-----|
| 85°   | 0.0 |
| 87.5° | 0.0 |



(END OF REPORT)