

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433820

Luminaire Tested: **LAMR4B208R459730DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433820
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B208R459730DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1458.1 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433820

CATALOG NUMBER: LAMR4B208R459730DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433820

CATALOG NUMBER: LAMR4B208R459730DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	94	91	103	98	93	90	95	92	89		93	90	87		90
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	79	76	91	84	79	75	82	78	75		81	77	74		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1347370
5°	1346920
10°	1280282
15°	1124593
20°	860336
25°	502249
30°	205550
35°	86913
40°	47403
45°	30631
50°	23871
55°	20730
60°	16775
65°	13192
70°	12262
75°	10866
80°	11933
85°	7925



TEST NUMBER: P433820

CATALOG NUMBER: LAMR4B208R459730DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	254.5	17.5
10°-20°	599.4	41.1
20°-30°	422.3	29.0
30°-40°	103.9	7.1
40°-50°	36.3	2.5
50°-60°	21.5	1.5
60°-70°	11.9	0.8
70°-80°	6.6	0.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1276.2	87.5
0°-40°	1380.2	94.7
0°-60°	1437.9	98.6
0°-90°	1458.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1458.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2731	
5°	2720	254
15°	2202	599
25°	923	422
35°	144	104
45°	44	36
55°	24	21
65°	11	12
75°	6	7
85°	1	2
90°	0	



TEST NUMBER: P433820

CATALOG NUMBER: LAMR4B208R459730DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2730.9
2.5°	2723.9
5°	2719.6
7.5°	2670.1
10°	2555.5
12.5°	2399.8
15°	2201.7
17.5°	1945.6
20°	1638.6
22.5°	1286.2
25°	922.6
27.5°	595.7
30°	360.8
32.5°	219.3
35°	144.3
37.5°	101.9
40°	73.6
42.5°	56.6
45°	43.9
47.5°	36.8
50°	31.1
52.5°	26.9
55°	24.1
57.5°	21.2
60°	17.0
62.5°	14.1
65°	11.3
67.5°	9.9
70°	8.5
72.5°	7.1
75°	5.7
77.5°	5.7
80°	4.2
82.5°	2.8
85°	1.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)