

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433990

Luminaire Tested: **LAMR4B308R209024DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R209024DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2144.9 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433990

CATALOG NUMBER: LAMR4B308R209024DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P433990

CATALOG NUMBER: LAMR4B308R209024DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	101	100	99	99	97	97	97
2	112	108	105	103	110	106	104	102	103	101	100	101	99	97	98	97	95	94	94	94
3	108	104	100	98	107	103	100	97	100	98	96	98	96	94	96	94	93	91	91	91
4	105	100	97	94	104	99	96	93	97	94	92	96	93	91	94	92	90	89	89	89
5	103	97	93	90	101	96	93	90	95	92	89	93	91	89	92	90	88	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83	83	83
8	96	90	86	83	95	89	86	83	88	85	83	87	85	82	87	84	82	81	81	81
9	94	88	84	81	93	87	84	81	86	83	81	86	83	81	85	82	81	80	80	80
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	83	81	79	78	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7409179
5°	6262665
10°	3678474
15°	1317108
20°	435786
25°	173441
30°	82892
35°	47401
40°	34200
45°	28817
50°	33235
55°	27096
60°	13617
65°	11441
70°	14137
75°	15060
80°	11081
85°	11322



TEST NUMBER: P433990

CATALOG NUMBER: LAMR4B308R209024DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1035.4	48.3
10°-20°	807.5	37.6
20°-30°	167.6	7.8
30°-40°	52.8	2.5
40°-50°	34.0	1.6
50°-60°	27.3	1.3
60°-70°	10.7	0.5
70°-80°	8.0	0.4
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2010.5	93.7
0°-40°	2063.3	96.2
0°-60°	2124.6	99.1
0°-90°	2144.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2144.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15017	
5°	12645	###
15°	2579	807
25°	319	168
35°	79	53
45°	41	34
55°	32	27
65°	10	11
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P433990

CATALOG NUMBER: LAMR4B308R209024DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	15017.2
2.5°	14466.5
5°	12645.1
7.5°	10131.4
10°	7342.4
12.5°	4632.0
15°	2578.6
17.5°	1418.1
20°	830.0
22.5°	507.5
25°	318.6
27.5°	210.5
30°	145.5
32.5°	102.3
35°	78.7
37.5°	62.9
40°	53.1
42.5°	45.2
45°	41.3
47.5°	41.3
50°	43.3
52.5°	41.3
55°	31.5
57.5°	21.6
60°	13.8
62.5°	11.8
65°	9.8
67.5°	9.8
70°	9.8
72.5°	9.8
75°	7.9
77.5°	5.9
80°	3.9
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)