

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434091

Luminaire Tested: **LAMR4B308R409027DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R409027DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2505.2 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434091

CATALOG NUMBER: LAMR4B308R409027DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P434091

CATALOG NUMBER: LAMR4B308R409027DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	94	92		94
4	103	98	93	90	102	97	93	90	95	91	89		93	90	88		91
5	100	94	89	86	98	93	89	86	91	88	85		90	87	84		88
6	97	90	85	82	95	89	85	82	88	84	82		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	83	79	76	90	83	79	76	82	78	75		81	78	75		80
9	88	81	76	73	87	80	76	73	79	75	73		79	75	73		78
10	85	78	73	71	84	77	73	70	77	73	70		76	73	70		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	944439
5°	949259
10°	942519
15°	850296
20°	536463
25°	193206
30°	40479
35°	12312
40°	2461
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434091

CATALOG NUMBER: LAMR4B308R409027DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	556.6	22.2
10°-20°	1330.9	53.1
20°-30°	567.5	22.7
30°-40°	48.7	1.9
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2455.1	98.0
0°-40°	2503.7	99.9
0°-60°	2505.2	100.0
0°-90°	2505.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2505.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5862	
5°	5870	557
15°	5098	1331
25°	1087	568
35°	63	49
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434091

CATALOG NUMBER: LAMR4B308R409027DE01021MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5862.3
2.5°	5857.0
5°	5869.8
7.5°	5834.7
10°	5761.5
12.5°	5542.8
15°	5098.1
17.5°	4229.8
20°	3129.1
22.5°	2060.3
25°	1086.9
27.5°	440.5
30°	217.6
32.5°	115.7
35°	62.6
37.5°	31.8
40°	11.7
42.5°	2.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)