

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434186

Luminaire Tested: **LAMR4B308R609027DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R609027DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2201.5 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434186

CATALOG NUMBER: LAMR4B308R609027DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434186

CATALOG NUMBER: LAMR4B308R609027DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1248300
5°	1206464
10°	1195214
15°	1165558
20°	1075657
25°	963288
30°	745403
35°	446549
40°	171578
45°	62727
50°	2456
55°	1806
60°	2072
65°	1284
70°	1587
75°	2097
80°	3125
85°	0



TEST NUMBER: P434186

CATALOG NUMBER: LAMR4B308R609027DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	231.3	10.5
10°-20°	634.8	28.8
20°-30°	791.9	36.0
30°-40°	461.4	21.0
40°-50°	77.0	3.5
50°-60°	2.0	0.1
60°-70°	1.5	0.1
70°-80°	1.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1658.1	75.3
0°-40°	2119.4	96.3
0°-60°	2198.4	99.9
0°-90°	2201.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2201.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2530	
5°	2436	231
15°	2282	635
25°	1770	792
35°	741	461
45°	90	77
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P434186

CATALOG NUMBER: LAMR4B308R609027DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2530.1
2.5°	2488.4
5°	2436.0
7.5°	2406.0
10°	2385.7
12.5°	2352.5
15°	2281.9
17.5°	2176.0
20°	2048.7
22.5°	1919.2
25°	1769.5
27.5°	1561.9
30°	1308.4
32.5°	1024.9
35°	741.4
37.5°	467.5
40°	266.4
42.5°	156.2
45°	89.9
47.5°	31.0
50°	3.2
52.5°	2.1
55°	2.1
57.5°	2.1
60°	2.1
62.5°	2.1
65°	1.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)