

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434207

Luminaire Tested: **LAMR4B308R659024DE01021MMS**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P434207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-22)  
Test Lab: INNOVATION CENTER (G2)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B308R659024DE01021MMS  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 65 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2063.1 lumens  
Efficiency: N/A  
Efficacy: 64.7 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.97  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 31.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P434207

CATALOG NUMBER: LAMR4B308R659024DE01021MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P434207

CATALOG NUMBER: LAMR4B308R659024DE01021MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 |  | 104 | 102 | 100 |  |  | 100 | 99  | 97  |  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  |  | 97  | 94  | 91  |  |  | 94  | 91  | 89  |  |  | 91  |
| 3   | 101 | 94  | 89  | 85  | 99  | 93  | 88  | 84  |  | 90  | 86  | 83  |  |  | 88  | 84  | 81  |  |  | 86  |
| 4   | 96  | 88  | 82  | 77  | 94  | 86  | 81  | 77  |  | 84  | 80  | 76  |  |  | 82  | 78  | 75  |  |  | 80  |
| 5   | 90  | 82  | 75  | 71  | 89  | 81  | 75  | 70  |  | 79  | 74  | 70  |  |  | 77  | 73  | 69  |  |  | 75  |
| 6   | 85  | 76  | 70  | 65  | 84  | 75  | 69  | 65  |  | 74  | 68  | 64  |  |  | 72  | 68  | 64  |  |  | 71  |
| 7   | 81  | 71  | 65  | 60  | 80  | 70  | 64  | 60  |  | 69  | 64  | 60  |  |  | 68  | 63  | 59  |  |  | 67  |
| 8   | 77  | 67  | 60  | 56  | 75  | 66  | 60  | 56  |  | 65  | 59  | 56  |  |  | 64  | 59  | 55  |  |  | 63  |
| 9   | 73  | 63  | 56  | 52  | 72  | 62  | 56  | 52  |  | 61  | 56  | 52  |  |  | 60  | 55  | 52  |  |  | 59  |
| 10  | 69  | 59  | 53  | 49  | 68  | 58  | 53  | 49  |  | 58  | 52  | 48  |  |  | 57  | 52  | 48  |  |  | 56  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 982516 |
| 5°  | 942834 |
| 10° | 920520 |
| 15° | 894792 |
| 20° | 833297 |
| 25° | 769705 |
| 30° | 690939 |
| 35° | 507623 |
| 40° | 274177 |
| 45° | 117919 |
| 50° | 65703  |
| 55° | 46020  |
| 60° | 29504  |
| 65° | 22532  |
| 70° | 18465  |
| 75° | 16394  |
| 80° | 18184  |
| 85° | 11888  |



TEST NUMBER: P434207

CATALOG NUMBER: LAMR4B308R659024DE01021MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 179.9  | 8.7       |
| 10°-20°   | 488.8  | 23.7      |
| 20°-30°   | 648.0  | 31.4      |
| 30°-40°   | 513.2  | 24.9      |
| 40°-50°   | 152.9  | 7.4       |
| 50°-60°   | 48.9   | 2.4       |
| 60°-70°   | 19.5   | 0.9       |
| 70°-80°   | 9.3    | 0.5       |
| 80°-90°   | 2.6    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1316.7 | 63.8      |
| 0°-40°    | 1829.9 | 88.7      |
| 0°-60°    | 2031.7 | 98.5      |
| 0°-90°    | 2063.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2063.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1991 |      |
| 5°  | 1904 | 180  |
| 15° | 1752 | 489  |
| 25° | 1414 | 648  |
| 35° | 843  | 513  |
| 45° | 169  | 153  |
| 55° | 54   | 49   |
| 65° | 19   | 20   |
| 75° | 9    | 9    |
| 85° | 2    | 3    |
| 90° | 0    |      |



TEST NUMBER: P434207

CATALOG NUMBER: LAMR4B308R659024DE01021MMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1991.4 |
| 1°    | 1978.5 |
| 2°    | 1959.3 |
| 3°    | 1937.9 |
| 4°    | 1918.7 |
| 5°    | 1903.7 |
| 6°    | 1893.0 |
| 7°    | 1882.3 |
| 8°    | 1865.2 |
| 9°    | 1850.2 |
| 10°   | 1837.4 |
| 11°   | 1822.4 |
| 12°   | 1805.3 |
| 13°   | 1790.3 |
| 14°   | 1773.2 |
| 15°   | 1751.8 |
| 16°   | 1728.3 |
| 17°   | 1698.3 |
| 18°   | 1664.1 |
| 19°   | 1627.8 |
| 20°   | 1587.1 |
| 21°   | 1548.6 |
| 22°   | 1508.0 |
| 23°   | 1471.6 |
| 24°   | 1441.7 |
| 25°   | 1413.9 |
| 26°   | 1383.9 |
| 27°   | 1354.0 |
| 28°   | 1315.5 |
| 29°   | 1268.4 |
| 30°   | 1212.8 |
| 32.5° | 1043.8 |
| 35°   | 842.8  |
| 37.5° | 624.6  |
| 40°   | 425.7  |
| 42.5° | 269.5  |
| 45°   | 169.0  |
| 47.5° | 113.4  |
| 50°   | 85.6   |
| 52.5° | 68.4   |
| 55°   | 53.5   |
| 57.5° | 40.6   |
| 60°   | 29.9   |



TEST NUMBER: P434207

CATALOG NUMBER: LAMR4B308R659024DE01021MMS

CANDELA DISTRIBUTION (continued):

|       | 0°   |
|-------|------|
| 67.5° | 15.0 |
| 70°   | 12.8 |
| 72.5° | 10.7 |
| 75°   | 8.6  |
| 77.5° | 6.4  |
| 80°   | 6.4  |
| 82.5° | 4.3  |
| 85°   | 2.1  |
| 87.5° | 0.0  |
| 90°   | 0.0  |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |      |
|-------|------|
| 62.5° | 23.5 |
| 65°   | 19.3 |



(END OF REPORT)