

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434231

Luminaire Tested: **LAMR4B308R709024DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434231
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R709024DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2076.8 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434231

CATALOG NUMBER: LAMR4B308R709024DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434231

CATALOG NUMBER: LAMR4B308R709024DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	104	110	107	105	103		103	101	100			100	98	97			96
2	106	101	96	92	104	99	95	91		96	92	89			93	90	87			90
3	100	93	87	83	98	91	86	82		89	84	81			86	82	79			84
4	94	85	79	74	92	84	78	74		82	77	73			80	76	72			78
5	88	79	72	68	87	78	72	67		76	71	67			74	70	66			73
6	83	73	66	62	82	72	66	61		71	65	61			69	64	60			68
7	78	68	61	56	77	67	61	56		66	60	56			65	59	56			63
8	74	63	57	52	73	63	56	52		62	56	52			60	55	51			59
9	70	59	53	48	69	59	52	48		58	52	48			57	51	48			56
10	66	55	49	45	65	55	49	44		54	48	44			53	48	44			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	753144
5°	739132
10°	747679
15°	768832
20°	770134
25°	698663
30°	624283
35°	548339
40°	403698
45°	226139
50°	111297
55°	62363
60°	37892
65°	24866
70°	18465
75°	16203
80°	12217
85°	11888



TEST NUMBER: P434231

CATALOG NUMBER: LAMR4B308R709024DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.7	6.9
10°-20°	424.1	20.4
20°-30°	588.6	28.3
30°-40°	553.8	26.7
40°-50°	264.4	12.7
50°-60°	69.9	3.4
60°-70°	22.0	1.1
70°-80°	9.0	0.4
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.4	55.6
0°-40°	1709.1	82.3
0°-60°	2043.4	98.4
0°-90°	2076.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2076.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1526	
5°	1492	143
15°	1505	424
25°	1283	589
35°	910	554
45°	324	264
55°	72	70
65°	21	22
75°	8	9
85°	2	2
90°	0	



TEST NUMBER: P434231

CATALOG NUMBER: LAMR4B308R709024DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1526.5
2.5°	1507.3
5°	1492.4
7.5°	1490.3
10°	1492.4
12.5°	1496.6
15°	1505.2
17.5°	1505.2
20°	1466.8
22.5°	1385.8
25°	1283.4
27.5°	1181.1
30°	1095.8
32.5°	1012.7
35°	910.4
37.5°	778.2
40°	626.8
42.5°	466.9
45°	324.1
47.5°	215.3
50°	145.0
52.5°	100.2
55°	72.5
57.5°	51.2
60°	38.4
62.5°	27.7
65°	21.3
67.5°	14.9
70°	12.8
72.5°	10.7
75°	8.5
77.5°	6.4
80°	4.3
82.5°	4.3
85°	2.1
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)