

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432796

Luminaire Tested: **LAM4B308R309030DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B308R309030DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2425.7 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432796

CATALOG NUMBER: LAM4B308R309030DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P432796

CATALOG NUMBER: LAM4B308R309030DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	91	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4395074
5°	4299042
10°	3727521
15°	2310328
20°	846790
25°	283025
30°	138951
35°	69265
40°	42959
45°	27282
50°	19419
55°	15827
60°	13617
65°	10740
70°	13271
75°	13153
80°	13070
85°	13020



TEST NUMBER: P432796

CATALOG NUMBER: LAM4B308R309030DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	791.1	32.6
10°-20°	1194.4	49.2
20°-30°	291.2	12.0
30°-40°	79.7	3.3
40°-50°	32.1	1.3
50°-60°	17.2	0.7
60°-70°	10.2	0.4
70°-80°	7.9	0.3
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2276.7	93.9
0°-40°	2356.4	97.1
0°-60°	2405.7	99.2
0°-90°	2425.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2425.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8908	
5°	8680	791
15°	4523	1194
25°	520	291
35°	115	80
45°	39	32
55°	18	17
65°	9	10
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P432796

CATALOG NUMBER: LAM4B308R309030DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	8908.1
2.5°	8848.3
5°	8680.3
7.5°	8280.0
10°	7440.3
12.5°	6124.3
15°	4523.1
17.5°	2914.9
20°	1612.8
22.5°	860.4
25°	519.9
27.5°	352.0
30°	243.9
32.5°	165.6
35°	115.0
37.5°	85.1
40°	66.7
42.5°	50.6
45°	39.1
47.5°	32.2
50°	25.3
52.5°	23.0
55°	18.4
57.5°	16.1
60°	13.8
62.5°	11.5
65°	9.2
67.5°	9.2
70°	9.2
72.5°	9.2
75°	6.9
77.5°	6.9
80°	4.6
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)