

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433948

Luminaire Tested: **LAMR4B308R109030DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2008-908-1)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R109030DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 10 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2349.2 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433948

CATALOG NUMBER: LAMR4B308R109030DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P433948

CATALOG NUMBER: LAMR4B308R109030DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	116	114	112	111		113	112	110	109		108	107	106			104	103	103			98
2	113	110	107	105		111	108	106	104		105	103	102			102	101	99			96
3	110	106	103	101		108	105	102	100		102	100	98			100	98	97			94
4	108	103	100	97		106	102	99	97		100	98	96			98	96	95			93
5	105	101	97	95		104	100	97	94		98	96	94			97	95	93			91
6	103	98	95	93		102	98	95	92		97	94	92			95	93	91			90
7	102	97	93	91		101	96	93	91		95	92	90			94	92	90			89
8	100	95	92	89		99	94	91	89		94	91	89			93	90	89			88
9	98	93	90	88		98	93	90	88		92	90	88			92	89	88			87
10	97	92	89	87		96	92	89	87		91	88	87			90	88	86			86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16989179
5°	11411877
10°	2912510
15°	753968
20°	337813
25°	160702
30°	86253
35°	50172
40°	39030
45°	21142
50°	17424
55°	12989
60°	14900
65°	8873
70°	10963
75°	14488
80°	0
85°	0



TEST NUMBER: P433948

CATALOG NUMBER: LAMR4B308R109030DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1583.5	67.4
10°-20°	504.2	21.5
20°-30°	147.3	6.3
30°-40°	56.0	2.4
40°-50°	26.7	1.1
50°-60°	16.0	0.7
60°-70°	8.4	0.4
70°-80°	7.0	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2235.0	95.1
0°-40°	2291.0	97.5
0°-60°	2333.7	99.3
0°-90°	2349.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2349.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	34434	
5°	23042	###
15°	1476	504
25°	295	147
35°	83	56
45°	30	27
55°	15	16
65°	8	8
75°	8	7
85°	0	0
90°	0	



TEST NUMBER: P433948

CATALOG NUMBER: LAMR4B308R109030DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	34434.3
1°	34101.2
2°	32723.5
3°	30096.9
4°	26849.5
5°	23042.0
6°	18833.3
7°	14950.0
8°	11165.2
9°	8137.4
10°	5813.5
11°	4117.9
12°	3050.6
13°	2316.3
14°	1839.4
15°	1476.1
17.5°	961.3
20°	643.4
22.5°	431.5
25°	295.2
27.5°	204.4
30°	151.4
32.5°	106.0
35°	83.3
37.5°	68.1
40°	60.6
42.5°	45.4
45°	30.3
47.5°	22.7
50°	22.7
52.5°	22.7
55°	15.1
57.5°	15.1
60°	15.1
62.5°	7.6
65°	7.6
67.5°	7.6
70°	7.6
72.5°	7.6
75°	7.6
77.5°	7.6
80°	0.0
82.5°	0.0



TEST NUMBER: P433948

CATALOG NUMBER: LAMR4B308R109030DE01021MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)