

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434045

Luminaire Tested: **LAMR4B308R309030DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434045
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R309030DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2425.7 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434045

CATALOG NUMBER: LAMR4B308R309030DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434045

CATALOG NUMBER: LAMR4B308R309030DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	111	109	107		107	105	104		103	102	101		100	99	98
2	111	107	104	102		109	106	103	100		102	100	98		100	98	96		97	95	94
3	107	103	99	96		105	101	98	95		99	96	94		96	94	92		94	92	91
4	104	98	94	91		102	97	94	91		95	92	90		93	91	89		92	90	88
5	101	95	91	87		99	94	90	87		92	89	86		91	88	86		89	87	85
6	98	91	87	84		97	91	87	84		89	86	83		88	85	83		87	84	82
7	95	88	84	81		94	88	84	81		87	83	81		86	83	80		85	82	80
8	92	86	81	79		91	85	81	78		84	81	78		83	80	78		83	80	78
9	90	83	79	76		89	83	79	76		82	78	76		81	78	76		80	78	75
10	88	81	77	74		87	80	77	74		80	76	74		79	76	74		78	76	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4395074
5°	4299042
10°	3727521
15°	2310328
20°	846790
25°	283025
30°	138951
35°	69265
40°	42959
45°	27282
50°	19419
55°	15827
60°	13617
65°	10740
70°	13271
75°	13153
80°	13070
85°	13020



TEST NUMBER: P434045

CATALOG NUMBER: LAMR4B308R309030DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	791.1	32.6
10°-20°	1194.4	49.2
20°-30°	291.2	12.0
30°-40°	79.7	3.3
40°-50°	32.1	1.3
50°-60°	17.2	0.7
60°-70°	10.2	0.4
70°-80°	7.9	0.3
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2276.7	93.9
0°-40°	2356.4	97.1
0°-60°	2405.7	99.2
0°-90°	2425.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2425.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8908	
5°	8680	791
15°	4523	1194
25°	520	291
35°	115	80
45°	39	32
55°	18	17
65°	9	10
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P434045

CATALOG NUMBER: LAMR4B308R309030DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8908.1
2.5°	8848.3
5°	8680.3
7.5°	8280.0
10°	7440.3
12.5°	6124.3
15°	4523.1
17.5°	2914.9
20°	1612.8
22.5°	860.4
25°	519.9
27.5°	352.0
30°	243.9
32.5°	165.6
35°	115.0
37.5°	85.1
40°	66.7
42.5°	50.6
45°	39.1
47.5°	32.2
50°	25.3
52.5°	23.0
55°	18.4
57.5°	16.1
60°	13.8
62.5°	11.5
65°	9.2
67.5°	9.2
70°	9.2
72.5°	9.2
75°	6.9
77.5°	6.9
80°	4.6
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)