

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434161

Luminaire Tested: **LAMR4B308R559027DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R559027DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2337.8 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434161

CATALOG NUMBER: LAMR4B308R559027DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P434161

CATALOG NUMBER: LAMR4B308R559027DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	110	108	106		105	104	102		102	101	99		98	97	97
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82
5	96	89	83	80		94	88	83	79		86	82	79		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	78	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	70		77	73	70		76	72	70
8	84	76	71	67		83	75	70	67		74	70	67		73	69	66		72	69	66
9	81	72	67	64		80	72	67	63		71	66	63		70	66	63		69	66	63
10	78	69	64	60		77	69	64	60		68	63	60		67	63	60		66	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1573387
5°	1595444
10°	1632779
15°	1564481
20°	1421450
25°	1142336
30°	657611
35°	190871
40°	29176
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434161

CATALOG NUMBER: LAMR4B308R559027DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	308.9	13.2
10°-20°	852.2	36.5
20°-30°	919.8	39.3
30°-40°	251.6	10.8
40°-50°	5.3	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2080.9	89.0
0°-40°	2332.5	99.8
0°-60°	2337.8	100.0
0°-90°	2337.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2337.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3189	
5°	3221	309
15°	3063	852
25°	2098	920
35°	317	252
45°	0	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434161

CATALOG NUMBER: LAMR4B308R559027DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3189.0
2.5°	3176.1
5°	3221.4
7.5°	3256.9
10°	3259.1
12.5°	3176.1
15°	3062.9
17.5°	2913.1
20°	2707.3
22.5°	2442.2
25°	2098.4
27.5°	1659.7
30°	1154.3
32.5°	632.6
35°	316.9
37.5°	135.8
40°	45.3
42.5°	6.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)