

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434189

Luminaire Tested: **LAMR4B308R609030DE01021MMS**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P434189  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B308R609030DE01021MMS  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2264.2 lumens  
Efficiency: N/A  
Efficacy: 71.0 lumens/watt  
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 31.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P434189

CATALOG NUMBER: LAMR4B308R609030DE01021MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P434189

CATALOG NUMBER: LAMR4B308R609030DE01021MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 |  | 105 | 103 | 102 |  |  | 101 | 100 | 99  |  |  | 98  |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  |  | 99  | 96  | 93  |  |  | 96  | 93  | 91  |  |  | 93  |
| 3   | 103 | 97  | 92  | 88  | 101 | 96  | 91  | 88  |  | 93  | 89  | 86  |  |  | 91  | 87  | 85  |  |  | 88  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  |  | 88  | 83  | 80  |  |  | 86  | 82  | 79  |  |  | 84  |
| 5   | 93  | 85  | 80  | 75  | 92  | 84  | 79  | 75  |  | 83  | 78  | 74  |  |  | 81  | 77  | 74  |  |  | 79  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  |  | 78  | 73  | 69  |  |  | 76  | 72  | 69  |  |  | 75  |
| 7   | 84  | 75  | 70  | 66  | 83  | 75  | 69  | 65  |  | 74  | 69  | 65  |  |  | 72  | 68  | 65  |  |  | 71  |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  |  | 70  | 65  | 61  |  |  | 69  | 64  | 61  |  |  | 68  |
| 9   | 77  | 67  | 62  | 58  | 76  | 67  | 61  | 58  |  | 66  | 61  | 57  |  |  | 65  | 60  | 57  |  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  |  | 62  | 58  | 54  |  |  | 62  | 57  | 54  |  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1283922 |
| 5°  | 1240835 |
| 10° | 1229281 |
| 15° | 1198810 |
| 20° | 1106319 |
| 25° | 990725  |
| 30° | 766653  |
| 35° | 459258  |
| 40° | 176473  |
| 45° | 64472   |
| 50° | 2533    |
| 55° | 1892    |
| 60° | 2171    |
| 65° | 1284    |
| 70° | 1587    |
| 75° | 2097    |
| 80° | 3125    |
| 85° | 0       |



TEST NUMBER: P434189

CATALOG NUMBER: LAMR4B308R609030DE01021MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 237.9  | 10.5      |
| 10°-20°   | 652.9  | 28.8      |
| 20°-30°   | 814.5  | 36.0      |
| 30°-40°   | 474.5  | 21.0      |
| 40°-50°   | 79.2   | 3.5       |
| 50°-60°   | 2.1    | 0.1       |
| 60°-70°   | 1.5    | 0.1       |
| 70°-80°   | 1.2    | 0.1       |
| 80°-90°   | 0.4    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1705.4 | 75.3      |
| 0°-40°    | 2179.9 | 96.3      |
| 0°-60°    | 2261.1 | 99.9      |
| 0°-90°    | 2264.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2264.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2602 |      |
| 5°  | 2505 | 238  |
| 15° | 2347 | 653  |
| 25° | 1820 | 815  |
| 35° | 762  | 475  |
| 45° | 92   | 79   |
| 55° | 2    | 2    |
| 65° | 1    | 1    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P434189

CATALOG NUMBER: LAMR4B308R609030DE01021MMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2602.3 |
| 2.5°  | 2559.4 |
| 5°    | 2505.4 |
| 7.5°  | 2474.6 |
| 10°   | 2453.7 |
| 12.5° | 2419.6 |
| 15°   | 2347.0 |
| 17.5° | 2238.1 |
| 20°   | 2107.1 |
| 22.5° | 1974.0 |
| 25°   | 1819.9 |
| 27.5° | 1606.5 |
| 30°   | 1345.7 |
| 32.5° | 1054.1 |
| 35°   | 762.5  |
| 37.5° | 480.8  |
| 40°   | 274.0  |
| 42.5° | 160.6  |
| 45°   | 92.4   |
| 47.5° | 31.9   |
| 50°   | 3.3    |
| 52.5° | 2.2    |
| 55°   | 2.2    |
| 57.5° | 2.2    |
| 60°   | 2.2    |
| 62.5° | 2.2    |
| 65°   | 1.1    |
| 67.5° | 1.1    |
| 70°   | 1.1    |
| 72.5° | 1.1    |
| 75°   | 1.1    |
| 77.5° | 1.1    |
| 80°   | 1.1    |
| 82.5° | 1.1    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)