

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434001

Luminaire Tested: **LAMR4B308R209035DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-3)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R209035DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 20 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2520.5 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.33
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434001

CATALOG NUMBER: LAMR4B308R209035DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P434001

CATALOG NUMBER: LAMR4B308R209035DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	115	113	111	110		113	111	109	108		107	106	105			103	102	102			100
2	112	108	105	103		110	106	104	102		103	101	100			101	99	97			98
3	108	104	100	98		107	103	100	97		100	98	95			98	96	94			96
4	105	100	97	94		104	99	96	93		97	94	92			95	93	91			94
5	103	97	93	90		101	96	93	90		95	92	89			93	91	89			92
6	100	94	90	88		99	94	90	87		92	89	87			91	88	86			90
7	98	92	88	85		97	91	88	85		90	87	85			89	86	84			88
8	96	90	86	83		95	89	86	83		88	85	83			87	85	82			87
9	94	88	84	81		93	87	84	81		86	83	81			86	83	81			85
10	92	86	82	80		91	85	82	80		85	82	79			84	81	79			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8706620
5°	7359329
10°	4322598
15°	1547727
20°	512127
25°	203817
30°	97420
35°	55713
40°	40189
45°	33841
50°	38992
55°	31827
60°	15985
65°	13542
70°	16734
75°	17538
80°	13070
85°	13020



TEST NUMBER: P434001

CATALOG NUMBER: LAMR4B308R209035DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1216.7	48.3
10°-20°	948.9	37.6
20°-30°	196.9	7.8
30°-40°	62.1	2.5
40°-50°	39.9	1.6
50°-60°	32.1	1.3
60°-70°	12.6	0.5
70°-80°	9.4	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2362.5	93.7
0°-40°	2424.6	96.2
0°-60°	2496.6	99.1
0°-90°	2520.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2520.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17647	
5°	14859	###
15°	3030	949
25°	374	197
35°	92	62
45°	48	40
55°	37	32
65°	12	13
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P434001

CATALOG NUMBER: LAMR4B308R209035DE01021MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	17646.9
2.5°	16999.7
5°	14859.4
7.5°	11905.6
10°	8628.1
12.5°	5443.1
15°	3030.1
17.5°	1666.5
20°	975.4
22.5°	596.3
25°	374.4
27.5°	247.3
30°	171.0
32.5°	120.2
35°	92.5
37.5°	74.0
40°	62.4
42.5°	53.2
45°	48.5
47.5°	48.5
50°	50.8
52.5°	48.5
55°	37.0
57.5°	25.4
60°	16.2
62.5°	13.9
65°	11.6
67.5°	11.6
70°	11.6
72.5°	11.6
75°	9.2
77.5°	6.9
80°	4.6
82.5°	2.3
85°	2.3
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)