

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434240

Luminaire Tested: **LAMR4B308R709035DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R709035DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2440.4 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434240

CATALOG NUMBER: LAMR4B308R709035DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434240

CATALOG NUMBER: LAMR4B308R709035DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	885024
5°	868545
10°	878587
15°	903475
20°	905018
25°	821040
30°	733610
35°	644346
40°	474416
45°	265701
50°	130793
55°	73287
60°	44503
65°	29303
70°	21638
75°	19063
80°	14206
85°	14152



TEST NUMBER: P434240

CATALOG NUMBER: LAMR4B308R709035DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.6	6.9
10°-20°	498.4	20.4
20°-30°	691.7	28.3
30°-40°	650.7	26.7
40°-50°	310.6	12.7
50°-60°	82.1	3.4
60°-70°	25.9	1.1
70°-80°	10.5	0.4
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1357.7	55.6
0°-40°	2008.4	82.3
0°-60°	2401.2	98.4
0°-90°	2440.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2440.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1794	
5°	1754	168
15°	1769	498
25°	1508	692
35°	1070	651
45°	381	311
55°	85	82
65°	25	26
75°	10	11
85°	2	3
90°	0	



TEST NUMBER: P434240

CATALOG NUMBER: LAMR4B308R709035DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1793.8
2.5°	1771.3
5°	1753.7
7.5°	1751.2
10°	1753.7
12.5°	1758.7
15°	1768.8
17.5°	1768.8
20°	1723.7
22.5°	1628.5
25°	1508.2
27.5°	1387.9
30°	1287.7
32.5°	1190.0
35°	1069.8
37.5°	914.4
40°	736.6
42.5°	548.7
45°	380.8
47.5°	253.0
50°	170.4
52.5°	117.7
55°	85.2
57.5°	60.1
60°	45.1
62.5°	32.6
65°	25.1
67.5°	17.5
70°	15.0
72.5°	12.5
75°	10.0
77.5°	7.5
80°	5.0
82.5°	5.0
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)