

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434243

Luminaire Tested: **LAMR4B308R709040DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R709040DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2595.1 lumens
Efficiency: N/A
Efficacy: 81.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434243

CATALOG NUMBER: LAMR4B308R709040DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434243

CATALOG NUMBER: LAMR4B308R709040DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63
8	74	63	57	52	73	63	56	52	62	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	941121
5°	923618
10°	934298
15°	960734
20°	962352
25°	873083
30°	780155
35°	685182
40°	504429
45°	282517
50°	139082
55°	77932
60°	47364
65°	31054
70°	23081
75°	20397
80°	15059
85°	15284



TEST NUMBER: P434243

CATALOG NUMBER: LAMR4B308R709040DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.3	6.9
10°-20°	530.0	20.4
20°-30°	735.5	28.3
30°-40°	692.0	26.7
40°-50°	330.3	12.7
50°-60°	87.3	3.4
60°-70°	27.5	1.1
70°-80°	11.2	0.4
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1443.8	55.6
0°-40°	2135.8	82.3
0°-60°	2553.4	98.4
0°-90°	2595.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2595.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1908	
5°	1865	178
15°	1881	530
25°	1604	735
35°	1138	692
45°	405	330
55°	91	87
65°	27	28
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P434243

CATALOG NUMBER: LAMR4B308R709040DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1907.5
2.5°	1883.5
5°	1864.9
7.5°	1862.2
10°	1864.9
12.5°	1870.2
15°	1880.9
17.5°	1880.9
20°	1832.9
22.5°	1731.7
25°	1603.8
27.5°	1475.9
30°	1369.4
32.5°	1265.5
35°	1137.6
37.5°	972.4
40°	783.2
42.5°	583.4
45°	404.9
47.5°	269.1
50°	181.2
52.5°	125.2
55°	90.6
57.5°	63.9
60°	48.0
62.5°	34.6
65°	26.6
67.5°	18.6
70°	16.0
72.5°	13.3
75°	10.7
77.5°	8.0
80°	5.3
82.5°	5.3
85°	2.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)