

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433982

Luminaire Tested: **LAMR4B308R159050DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-6)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R159050DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 15 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2787.3 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433982

CATALOG NUMBER: LAMR4B308R159050DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433982

CATALOG NUMBER: LAMR4B308R159050DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	102		102	101	100		100
3	110	106	103	101	108	105	102	100	103	100	98		100	99	97		98
4	108	103	100	97	106	102	99	97	100	98	96		98	96	95		97
5	105	101	97	95	104	100	97	94	98	96	94		97	95	93		95
6	103	98	95	92	102	98	94	92	96	94	92		95	93	91		94
7	101	96	93	90	100	96	92	90	95	92	90		94	91	89		93
8	99	94	91	89	99	94	91	89	93	90	88		92	90	88		91
9	98	92	89	87	97	92	89	87	91	89	87		91	88	87		90
10	96	91	88	86	95	91	88	86	90	87	85		89	87	85		89

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3987029
5°	3364907
10°	1545901
15°	482048
20°	196422
25°	64437
30°	19979
35°	4228
40°	1073
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P433982

CATALOG NUMBER: LAMR4B308R159050DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1605.6	57.6
10°-20°	956.9	34.3
20°-30°	202.8	7.3
30°-40°	21.4	0.8
40°-50°	0.7	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2765.2	99.2
0°-40°	2786.6	100.0
0°-60°	2787.3	100.0
0°-90°	2787.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2787.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24748	
5°	20807	###
15°	2890	957
25°	362	203
35°	22	21
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P433982

CATALOG NUMBER: LAMR4B308R159050DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	24748.2
2.5°	23966.3
5°	20807.1
7.5°	15403.2
10°	9449.9
12.5°	5042.6
15°	2890.2
17.5°	1815.2
20°	1145.7
22.5°	675.8
25°	362.5
27.5°	204.6
30°	107.4
32.5°	54.3
35°	21.5
37.5°	11.4
40°	5.1
42.5°	1.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)