

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434054

Luminaire Tested: **LAMR4B308R309050DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R309050DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2833.8 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434054

CATALOG NUMBER: LAMR4B308R309050DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434054

CATALOG NUMBER: LAMR4B308R309050DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5134354
5°	5022177
10°	4354511
15°	2698932
20°	989182
25°	330659
30°	162309
35°	80950
40°	50172
45°	31887
50°	22720
55°	18494
60°	15887
65°	12608
70°	15579
75°	15441
80°	15343
85°	15284



TEST NUMBER: P434054

CATALOG NUMBER: LAMR4B308R309050DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	924.2	32.6
10°-20°	1395.3	49.2
20°-30°	340.2	12.0
30°-40°	93.1	3.3
40°-50°	37.5	1.3
50°-60°	20.1	0.7
60°-70°	12.0	0.4
70°-80°	9.3	0.3
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2659.6	93.9
0°-40°	2752.8	97.1
0°-60°	2810.3	99.2
0°-90°	2833.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2833.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10406	
5°	10140	924
15°	5284	1395
25°	607	340
35°	134	93
45°	46	37
55°	22	20
65°	11	12
75°	8	9
85°	3	2
90°	0	



TEST NUMBER: P434054

CATALOG NUMBER: LAMR4B308R309050DE01021MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	10406.5
2.5°	10336.6
5°	10140.4
7.5°	9672.8
10°	8691.8
12.5°	7154.5
15°	5283.9
17.5°	3405.2
20°	1884.0
22.5°	1005.2
25°	607.4
27.5°	411.2
30°	284.9
32.5°	193.5
35°	134.4
37.5°	99.4
40°	77.9
42.5°	59.1
45°	45.7
47.5°	37.6
50°	29.6
52.5°	26.9
55°	21.5
57.5°	18.8
60°	16.1
62.5°	13.4
65°	10.8
67.5°	10.8
70°	10.8
72.5°	10.8
75°	8.1
77.5°	8.1
80°	5.4
82.5°	2.7
85°	2.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)