

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434198

Luminaire Tested: **LAMR4B308R609050DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R609050DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2645.2 lumens
Efficiency: N/A
Efficacy: 82.9 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434198

CATALOG NUMBER: LAMR4B308R609050DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434198

CATALOG NUMBER: LAMR4B308R609050DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1499874
5°	1449589
10°	1436090
15°	1400468
20°	1292447
25°	1157415
30°	895634
35°	536533
40°	206164
45°	75356
50°	2993
55°	2236
60°	2566
65°	1518
70°	1875
75°	2478
80°	3694
85°	0



TEST NUMBER: P434198

CATALOG NUMBER: LAMR4B308R609050DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.9	10.5
10°-20°	762.7	28.8
20°-30°	951.5	36.0
30°-40°	554.3	21.0
40°-50°	92.6	3.5
50°-60°	2.5	0.1
60°-70°	1.8	0.1
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1992.2	75.3
0°-40°	2546.5	96.3
0°-60°	2641.6	99.9
0°-90°	2645.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2645.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3040	
5°	2927	278
15°	2742	763
25°	2126	952
35°	891	554
45°	108	93
55°	3	2
65°	1	2
75°	1	1
85°	0	1
90°	0	



TEST NUMBER: P434198

CATALOG NUMBER: LAMR4B308R609050DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3040.0
2.5°	2989.9
5°	2926.9
7.5°	2890.9
10°	2866.5
12.5°	2826.6
15°	2741.8
17.5°	2614.5
20°	2461.6
22.5°	2306.0
25°	2126.1
27.5°	1876.7
30°	1572.1
32.5°	1231.4
35°	890.8
37.5°	561.7
40°	320.1
42.5°	187.7
45°	108.0
47.5°	37.3
50°	3.9
52.5°	2.6
55°	2.6
57.5°	2.6
60°	2.6
62.5°	2.6
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	1.3
80°	1.3
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)