

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434251

Luminaire Tested: **LAMR4B308R709730DE01021MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R709730DE01021MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2153.2 lumens
Efficiency: N/A
Efficacy: 67.5 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434251

CATALOG NUMBER: LAMR4B308R709730DE01021MB

Luminous Intensity Polar Plot





TEST NUMBER: P434251

CATALOG NUMBER: LAMR4B308R709730DE01021MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		65	59	56		63
8	74	63	57	52	73	63	56	52	62	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56
10	66	55	49	45	65	55	49	44	54	48	44		53	48	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	780872
5°	766322
10°	775183
15°	797130
20°	798486
25°	724412
30°	647300
35°	568516
40°	418575
45°	234442
50°	115365
55°	64686
60°	39273
65°	25800
70°	19186
75°	16775
80°	12502
85°	12454



TEST NUMBER: P434251

CATALOG NUMBER: LAMR4B308R709730DE01021MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	6.9
10°-20°	439.7	20.4
20°-30°	610.3	28.3
30°-40°	574.2	26.7
40°-50°	274.1	12.7
50°-60°	72.5	3.4
60°-70°	22.9	1.1
70°-80°	9.3	0.4
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1197.9	55.6
0°-40°	1772.1	82.3
0°-60°	2118.6	98.4
0°-90°	2153.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2153.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1583	
5°	1547	148
15°	1561	440
25°	1331	610
35°	944	574
45°	336	274
55°	75	72
65°	22	23
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P434251

CATALOG NUMBER: LAMR4B308R709730DE01021MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	1582.7
2.5°	1562.8
5°	1547.3
7.5°	1545.1
10°	1547.3
12.5°	1551.7
15°	1560.6
17.5°	1560.6
20°	1520.8
22.5°	1436.8
25°	1330.7
27.5°	1224.6
30°	1136.2
32.5°	1050.0
35°	943.9
37.5°	806.8
40°	649.9
42.5°	484.1
45°	336.0
47.5°	223.3
50°	150.3
52.5°	103.9
55°	75.2
57.5°	53.1
60°	39.8
62.5°	28.7
65°	22.1
67.5°	15.5
70°	13.3
72.5°	11.1
75°	8.8
77.5°	6.6
80°	4.4
82.5°	4.4
85°	2.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)