

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434201

Luminaire Tested: **LAMR4B308R609727DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B308R609727DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1952.9 lumens
Efficiency: N/A
Efficacy: 61.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434201

CATALOG NUMBER: LAMR4B308R609727DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434201

CATALOG NUMBER: LAMR4B308R609727DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	96	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	88	101	96	91	88	93	89	86		91	87	85		88
4	98	91	85	81	96	90	85	81	88	83	80		86	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71
8	80	71	65	61	79	71	65	61	70	65	61		69	64	61		68
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1107390
5°	1070266
10°	1060297
15°	1033980
20°	954214
25°	854520
30°	661257
35°	396136
40°	152192
45°	55610
50°	2149
55°	1634
60°	1875
65°	1051
70°	1298
75°	1716
80°	2557
85°	0



TEST NUMBER: P434201

CATALOG NUMBER: LAMR4B308R609727DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.2	10.5
10°-20°	563.1	28.8
20°-30°	702.5	36.0
30°-40°	409.3	21.0
40°-50°	68.3	3.5
50°-60°	1.8	0.1
60°-70°	1.3	0.1
70°-80°	1.0	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1470.9	75.3
0°-40°	1880.2	96.3
0°-60°	1950.3	99.9
0°-90°	1952.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1952.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2244	
5°	2161	205
15°	2024	563
25°	1570	703
35°	658	409
45°	80	68
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P434201

CATALOG NUMBER: LAMR4B308R609727DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2244.5
2.5°	2207.5
5°	2161.0
7.5°	2134.4
10°	2116.4
12.5°	2087.0
15°	2024.3
17.5°	1930.4
20°	1817.4
22.5°	1702.6
25°	1569.7
27.5°	1385.6
30°	1160.7
32.5°	909.2
35°	657.7
37.5°	414.7
40°	236.3
42.5°	138.6
45°	79.7
47.5°	27.5
50°	2.8
52.5°	1.9
55°	1.9
57.5°	1.9
60°	1.9
62.5°	1.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)