

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432717

Luminaire Tested: **LAM4B308R109730DE01021MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432717
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2008-908-1)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B308R109730DE01021MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 10 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2171.2 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 31.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432717

CATALOG NUMBER: LAM4B308R109730DE01021MW

Luminous Intensity Polar Plot





TEST NUMBER: P432717

CATALOG NUMBER: LAM4B308R109730DE01021MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	112	111	113	112	110	109	108	107	106		104	103	103		101
2	113	110	107	105	111	108	106	104	105	103	102		102	101	99		99
3	110	106	103	101	108	105	102	100	102	100	98		100	98	97		98
4	108	103	100	97	106	102	99	97	100	98	96		98	96	95		97
5	105	101	97	95	104	100	97	94	98	96	94		97	95	93		96
6	103	98	95	93	102	98	95	92	97	94	92		95	93	91		94
7	102	97	93	91	101	96	93	91	95	92	90		94	92	90		93
8	100	95	92	89	99	94	91	89	94	91	89		93	90	89		92
9	98	93	90	88	98	93	90	88	92	90	88		92	89	88		91
10	97	92	89	87	96	92	89	87	91	88	87		90	88	86		90

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15701853
5°	10547195
10°	2691823
15°	696812
20°	312243
25°	148508
30°	79702
35°	46378
40°	36067
45°	19537
50°	16119
55°	12043
60°	13815
65°	8172
70°	10098
75°	13344
80°	0
85°	0



TEST NUMBER: P432717

CATALOG NUMBER: LAM4B308R109730DE01021MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1463.6	67.4
10°-20°	466.0	21.5
20°-30°	136.1	6.3
30°-40°	51.8	2.4
40°-50°	24.7	1.1
50°-60°	14.8	0.7
60°-70°	7.8	0.4
70°-80°	6.5	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2065.6	95.1
0°-40°	2117.4	97.5
0°-60°	2156.9	99.3
0°-90°	2171.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2171.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	31825	
5°	21296	###
15°	1364	466
25°	273	136
35°	77	52
45°	28	25
55°	14	15
65°	7	8
75°	7	6
85°	0	0
90°	0	



TEST NUMBER: P432717

CATALOG NUMBER: LAM4B308R109730DE01021MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	31825.1
1°	31517.3
2°	30244.0
3°	27816.4
4°	24815.1
5°	21296.1
6°	17406.2
7°	13817.2
8°	10319.2
9°	7520.8
10°	5373.0
11°	3805.9
12°	2819.4
13°	2140.8
14°	1700.0
15°	1364.2
17.5°	888.5
20°	594.7
22.5°	398.8
25°	272.8
27.5°	188.9
30°	139.9
32.5°	97.9
35°	77.0
37.5°	63.0
40°	56.0
42.5°	42.0
45°	28.0
47.5°	21.0
50°	21.0
52.5°	21.0
55°	14.0
57.5°	14.0
60°	14.0
62.5°	7.0
65°	7.0
67.5°	7.0
70°	7.0
72.5°	7.0
75°	7.0
77.5°	7.0
80°	0.0
82.5°	0.0



TEST NUMBER: P432717

CATALOG NUMBER: LAM4B308R109730DE01021MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)