

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432861

Luminaire Tested: **LAM4B308R409730DE01021MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P432861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1911-585-7)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAM4B308R409730DE01021MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 40 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 97CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2381.4 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6  
Luminous Opening: Circular (Dia: 0.29' x H: 0')  
CIE Type: Direct


Input Watts (W): 31.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P432861

CATALOG NUMBER: LAM4B308R409730DE01021MW

### Luminous Intensity Polar Plot





TEST NUMBER: P432861

CATALOG NUMBER: LAM4B308R409730DE01021MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 |  | 103 | 102 | 101 |  | 99  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  |  | 99  | 97  | 96  |  | 97  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  |  | 96  | 94  | 92  |  | 94  |
| 4   | 103 | 98  | 93  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 89  |  | 93  | 90  | 88  |  | 91  |
| 5   | 100 | 94  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 88  | 85  |  | 90  | 87  | 84  |  | 88  |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  |  | 87  | 83  | 81  |  | 85  |
| 7   | 93  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  |  | 84  | 80  | 78  |  | 83  |
| 8   | 91  | 83  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 75  |  | 81  | 78  | 75  |  | 80  |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 75  | 73  |  | 79  | 75  | 73  |  | 78  |
| 10  | 85  | 78  | 73  | 71  | 84  | 77  | 73  | 70  | 77  | 73  | 70  |  | 76  | 73  | 70  |  | 75  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 897783 |
| 5°  | 902345 |
| 10° | 895945 |
| 15° | 808283 |
| 20° | 509957 |
| 25° | 183660 |
| 30° | 38470  |
| 35° | 11702  |
| 40° | 2334   |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P432861

CATALOG NUMBER: LAM4B308R409730DE01021MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 529.1  | 22.2      |
| 10°-20°   | 1265.2 | 53.1      |
| 20°-30°   | 539.5  | 22.7      |
| 30°-40°   | 46.3   | 1.9       |
| 40°-50°   | 1.4    | 0.1       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2333.8 | 98.0      |
| 0°-40°    | 2380.0 | 99.9      |
| 0°-60°    | 2381.4 | 100.0     |
| 0°-90°    | 2381.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2381.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5573 |      |
| 5°  | 5580 | 529  |
| 15° | 4846 | 1265 |
| 25° | 1033 | 539  |
| 35° | 60   | 46   |
| 45° | 0    | 1    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P432861

CATALOG NUMBER: LAM4B308R409730DE01021MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5572.7 |
| 2.5°  | 5567.6 |
| 5°    | 5579.7 |
| 7.5°  | 5546.4 |
| 10°   | 5476.8 |
| 12.5° | 5269.0 |
| 15°   | 4846.2 |
| 17.5° | 4020.8 |
| 20°   | 2974.5 |
| 22.5° | 1958.5 |
| 25°   | 1033.2 |
| 27.5° | 418.7  |
| 30°   | 206.8  |
| 32.5° | 110.0  |
| 35°   | 59.5   |
| 37.5° | 30.3   |
| 40°   | 11.1   |
| 42.5° | 2.0    |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)