

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434474

Luminaire Tested: **LAMR4B408R559027DE01021MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P434474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B408R559027DE01021MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3103.1 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 41.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P434474

CATALOG NUMBER: LAMR4B408R559027DE01021MMS

Luminous Intensity Polar Plot





TEST NUMBER: P434474

CATALOG NUMBER: LAMR4B408R559027DE01021MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	110	108	106		105	104	102		102	101	99		98	97	97
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82
5	96	89	83	80		94	88	83	79		86	82	79		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	78	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	70		77	73	70		76	72	70
8	84	76	71	67		83	75	70	67		74	70	67		73	69	66		72	69	66
9	81	72	67	64		80	72	67	63		71	66	63		70	66	63		69	66	63
10	78	69	64	60		77	69	64	60		68	63	60		67	63	60		66	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2088476
5°	2117700
10°	2167286
15°	2076644
20°	1886797
25°	1516273
30°	872846
35°	253330
40°	38708
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P434474

CATALOG NUMBER: LAMR4B408R559027DE01021MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	410.0	13.2
10°-20°	1131.2	36.5
20°-30°	1220.9	39.3
30°-40°	333.9	10.8
40°-50°	7.0	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2762.1	89.0
0°-40°	3096.1	99.8
0°-60°	3103.1	100.0
0°-90°	3103.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3103.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4233	
5°	4276	410
15°	4066	1131
25°	2785	1221
35°	421	334
45°	0	7
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P434474

CATALOG NUMBER: LAMR4B408R559027DE01021MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4233.0
2.5°	4215.8
5°	4275.9
7.5°	4323.1
10°	4326.0
12.5°	4215.8
15°	4065.6
17.5°	3866.8
20°	3593.6
22.5°	3241.6
25°	2785.3
27.5°	2203.1
30°	1532.1
32.5°	839.7
35°	420.6
37.5°	180.2
40°	60.1
42.5°	8.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)