

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P434499

Luminaire Tested: **LAMR4B408R609027DE01021MW**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P434499  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2009-969-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B408R609027DE01021MW  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 60 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2922.1 lumens  
Efficiency: N/A  
Efficacy: 70.9 lumens/watt  
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.89  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 41.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P434499

CATALOG NUMBER: LAMR4B408R609027DE01021MW

### Luminous Intensity Polar Plot





TEST NUMBER: P434499

CATALOG NUMBER: LAMR4B408R609027DE01021MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 108 | 104 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  |  | 96  | 93  | 91  |  | 93  |
| 3   | 103 | 97  | 92  | 88  | 101 | 96  | 91  | 88  | 93  | 89  | 86  |  | 91  | 87  | 85  |  | 88  |
| 4   | 98  | 91  | 85  | 81  | 96  | 90  | 85  | 81  | 88  | 83  | 80  |  | 86  | 82  | 79  |  | 84  |
| 5   | 93  | 85  | 80  | 75  | 92  | 84  | 79  | 75  | 83  | 78  | 74  |  | 81  | 77  | 74  |  | 79  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  |  | 76  | 72  | 69  |  | 75  |
| 7   | 84  | 75  | 70  | 66  | 83  | 75  | 69  | 65  | 74  | 69  | 65  |  | 72  | 68  | 65  |  | 71  |
| 8   | 80  | 71  | 65  | 61  | 79  | 71  | 65  | 61  | 70  | 65  | 61  |  | 69  | 64  | 61  |  | 68  |
| 9   | 77  | 67  | 62  | 58  | 76  | 67  | 61  | 58  | 66  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 58  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1656966 |
| 5°  | 1601387 |
| 10° | 1586487 |
| 15° | 1547114 |
| 20° | 1427803 |
| 25° | 1278595 |
| 30° | 989408  |
| 35° | 592729  |
| 40° | 227740  |
| 45° | 83241   |
| 50° | 3301    |
| 55° | 2409    |
| 60° | 2763    |
| 65° | 1634    |
| 70° | 2020    |
| 75° | 2669    |
| 80° | 3978    |
| 85° | 0       |



TEST NUMBER: P434499

CATALOG NUMBER: LAMR4B408R609027DE01021MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 307.0  | 10.5      |
| 10°-20°   | 842.6  | 28.8      |
| 20°-30°   | 1051.2 | 36.0      |
| 30°-40°   | 612.4  | 21.0      |
| 40°-50°   | 102.2  | 3.5       |
| 50°-60°   | 2.7    | 0.1       |
| 60°-70°   | 1.9    | 0.1       |
| 70°-80°   | 1.5    | 0.1       |
| 80°-90°   | 0.6    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2200.8 | 75.3      |
| 0°-40°    | 2813.2 | 96.3      |
| 0°-60°    | 2918.1 | 99.9      |
| 0°-90°    | 2922.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2922.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3358 |      |
| 5°  | 3233 | 307  |
| 15° | 3029 | 843  |
| 25° | 2349 | 1051 |
| 35° | 984  | 612  |
| 45° | 119  | 102  |
| 55° | 3    | 3    |
| 65° | 1    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P434499

CATALOG NUMBER: LAMR4B408R609027DE01021MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3358.4 |
| 2.5°  | 3303.0 |
| 5°    | 3233.4 |
| 7.5°  | 3193.7 |
| 10°   | 3166.7 |
| 12.5° | 3122.7 |
| 15°   | 3028.9 |
| 17.5° | 2888.3 |
| 20°   | 2719.4 |
| 22.5° | 2547.5 |
| 25°   | 2348.7 |
| 27.5° | 2073.2 |
| 30°   | 1736.7 |
| 32.5° | 1360.4 |
| 35°   | 984.1  |
| 37.5° | 620.6  |
| 40°   | 353.6  |
| 42.5° | 207.3  |
| 45°   | 119.3  |
| 47.5° | 41.2   |
| 50°   | 4.3    |
| 52.5° | 2.8    |
| 55°   | 2.8    |
| 57.5° | 2.8    |
| 60°   | 2.8    |
| 62.5° | 2.8    |
| 65°   | 1.4    |
| 67.5° | 1.4    |
| 70°   | 1.4    |
| 72.5° | 1.4    |
| 75°   | 1.4    |
| 77.5° | 1.4    |
| 80°   | 1.4    |
| 82.5° | 1.4    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)